

9070T3000D5

INDUSTRIAL CONTROL TRANSFORMER

3000VA MULTIPLE VOLTAGES

Main

Product or component type	Industrial Control Transformer
Power Rating	3000 VA 2000 VA
Primary Voltage	575 V 550 V 600 V
Secondary Voltage	120 V 110 V 115 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	3000 VA UL 3000 VA CSA 3000 VA NOM 2000 VA
Primary to Secondary Voltage	550 V 110 V 575 V 115 V 600 V 120 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	8.75 in (222.25 mm)
Width	9 in (228.60 mm)
Depth	7.24 in (183.90 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

Environment

Product certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16205 - 9070 T (NOT TF) 3000 - 5000VA
Discount Schedule	CP8
GTIN	00785901767923
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------