

# 9070KL300D3

## INDUSTRIAL CONTROL TRANSFORMER

### 300VA 208V PRIMARY WITH 610mm/24INCH LEADS

#### Main

Product or component type	Industrial Control Transformer
Range of product	KL

#### Complementary

Phase	1 phase
Rated power in VA	300 VA
Primary voltage	208 V
Secondary voltage	120 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Connector type	Lead 2001.31 ft (610 m)


#### Environment

Product certifications	CSA UL listed CE
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

#### Ordering and shipping details

Category	21692 - 9070 K (NOT KF)
Discount Schedule	CP8
GTIN	00785901939665
Returnability	No
Country of origin	US

#### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
<b>Contractual warranty</b>	
Warranty	18 months