

### Main

Product or component type	Industrial Control Transformer
Power Rating	150 VA
Primary Voltage	380/400/415 V
Secondary Voltage	115/230 V
Type	TF

### Complementary

Number of Phases	1 phase
Power Rating	150 VA
Primary to Secondary Voltage	380/400/415 V 115/230 V
Fuse type	10.3 x 38 mm CC top
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Height	4.5 in (114.30 mm)
Width	3.75 in (95.25 mm)
Depth	3.59 in (91.19 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC1




### Environment

Product certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

### Ordering and shipping details

Category	16202 - 9070 TF (NOT T) 50-200VA
Discount Schedule	CP8
GTIN	00785901707332
Returnability	Yes
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>

Contractual warranty

Warranty	18 months
----------	-----------