



Product #: 7032521
Order Symbol: UL PCT 050705
Description: Enclosure, PC
Remarks: Clear Cover

Dimensions	Length	Width	Height
Inch	1.8	2	2.6
mm	45	50	65

Materials		Temperatures	
Material:	Polycarbonate	Temperature °F (short term):	-40 ... 250
Base color:	RAL 7035 -light grey	Temperature °F (continuous):	-40 ... 175
Cover color:	Clear	Temperature °C (short term):	-40 ... 120
Gasket material:	Polyurethane	Temperature °C (continuous):	-40 ... 80

Ratings	
Ingress Protection (EN 60529):	IP66IP67
Impact Resistance (EN 62262):	IK07IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	No
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 60695):	960 °C
UL/cUL Type:	NEMA Type 1, 4, 4X, 12 and 13