



Product #: 8143352

Order Symbol: UL CAB PC 403018 G3B

Description: 15.7 x 11.8 x 7.1 inch polycarbonate enclosure with an opaque door, Locks long side, with 3mm double bit lock(s).

Dimensions	Length	Width	Height
Inch	7.1	11.8	15.7
mm	180	300	400

Materials

Material:	Polycarbonate
Base color:	RAL 7035 -light grey
Cover color:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures

Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175
Temperature °C (short term):	-40 ... 140
Temperature °C (continuous):	-40 ... 80

Ratings

Ingress Protection (EN 60529):	IP65
Impact Resistance (EN 62262):	IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	No
UV resistance:	UL 508
Flammability Rating:	UL94-5VA (f1)/ Cover: UL94-V0 (f1)
Glow Wire Test (IEC 60695):	960 °C
UL/cUL Type:	Type 1, 4, 4X, 12, and 13