



Product #: 7032640
Order Symbol: UL PC 081610
Description: Enclosure, PC
Remarks: Grey cover

Dimensions	Length	Width	Height
Inch	2.2	3.1	6.3
mm	95	80	160

Materials	
Material:	Polycarbonate
Base color:	RAL 7035 -light grey
Cover color:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures	
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175
Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80

Ratings	
Ingress Protection (EN 60529):	IP66/IP67
Impact Resistance (EN 62262):	IK07/IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	No
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 60695):	960 °C
UL/cUL Type:	NEMA Type 1, 4, 4X, 12 and 13