



**90-series, Phosphated, 90 ergo®**

As per DIN 3117 Form A, angle 15°, BS 6333, ISO 6787 and ASME B107.8M-1996.





**Finish:** Phosphated. Precision-hardened and anti-corrosion treated. With comfortable thermoplastic handle and larger grip width. The sixth generation of the adjustable wrench.

**Series P :** combination of pipe grip facility, one side serrated, may be used as a pipe wrench.

Left-reading, measurement scale in mm.

Single pack



			<b>A</b> mm	<b>B</b> mm	<b>C</b> mm	<b>D</b> mm 
9070	0100170	5	158	20	4.9	11.3 139
9070 P	0103416	5	158	21	4.9	11.3 139
9071	0100194	5	208	27	6.0	12.9 272
9071 P	0103430	5	208	28	6.0	12.9 272
9072	0055609	5	257	31	8.7	15.2 425
9072 P	0056354	5	257	33	8.7	15.2 430
9073	0101702	5	308	34	11.9	17.6 730
9073 P	0101726	5	308	35	11.9	17.6 745