



P1	P2	P1	P2
49	1	29	10
50	3	5	16
46	2	31	11
24	24	7	18
45	4	32	12
23	24	8	18
44	5	33	13
22	9	9	18
43	6	3	14
20	9	27	21
16	7	48	15
38	25	25	24
18	7	4	16
41	17	28	22
19	7	6	16
1	14	30	23
26	8	11	18
2	14	34	20
21	9		
47	19		
		SHIELD	SHIELD

7	BALCK HEAT SHRINK TUBE Ø3.0*10mm	6	M519
	PVC TUBE Ø3.0*30mm	1	M304
	COPPER FOIL 33*110mm	1	M309
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC LIGHT BEIGE		M304
6	PE HOOD COLOR TRANSPARENT	1	M304
	COPPER FOIL 7.5x30mm	1	M309
	COPPER FOIL 33x130mm	1	M309
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC LIGHT BEIGE		M304
5	UL2919 19 TWISTED PAIRS 28AWG, ALUM-MYLAR AND COPPER BRAID FOIL SHIELDING WITH DRAIN WIRE, OD 7.5mm, JACKET LIGHT BEIGE	2020mm	M2
4	LATCH	2	M110
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, LIGHT BEIGE	2	M95
2	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M83
1	HPDB50 MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR(0.62)	1set	M110
Na.	DESCRIPTION	Q'TY	Supplier

ITEM NO.
CS02395