



P1	P2	P1	P2
1	1	18	18
35	35	52	52
2	2	19	19
36	36	53	53
3	3	20	20
37	37	54	54
4	4	21	21
38	38	55	55
5	5	22	22
39	39	56	56
6	6	23	23
40	40	57	57
7	7	24	24
41	41	58	58
8	8	25	25
42	42	59	59
9	9	26	26
43	43	60	60
10	10	27	27
44	44	61	61
11	11	28	28
45	45	62	62
12	12	29	29
46	46	63	63
13	13	30	30
47	47	64	64
14	14	31	31
48	48	65	65
15	15	32	32
49	49	66	66
16	16	33	33
50	50	67	67
17	17	34	34
51	51	68	68
SHIELD	SHIELD	SHIELD	SHIELD

4	PE HOOD COLOR TRANSPARENT	2	M304
	COPPER FOIL 7.5*35mm	2	M309
	COPPER FOIL 33*150mm	2	M309
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC LIGHT BEIGE		M304
3	UL2919 34 TWISTED PAIRS 28AWG, ALUM-MYLAR FOIL AND COPPER BRAID SHIELDING WITH DRAIN WIRE, QD 11.5mm, JACKET LIGHT BEIGE	1040mm	M2
2	MOLDED THUMBSCREW #2-56, LENGTH 41mm, LIGHT BEIGE	4	M95
1	HPDB68 MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR (Q.75)	1set	M83
No.	DESCRIPTION	Q'TY	Supplier

ITEM NO.
CS02397