

5 SPEED HOBBY BENCH DRILL

CATALOGUE ENTRY

54 D13/5A
5 SPEED HOBBY BENCH DRILL

No-volt switch.

Five speed bench drill complete with 13mm capacity chuck ideally suited for the DIY and hobby user alike. Square table with a rise and fall adjustment featuring a 0-45° tilt, left and right for ease of use. Fitted with a BS approved non-rewireable 3 pin moulded plug and cable. Display carton.

Specification:

Drilling capacity	... 13mm
Chuck capacity	... 13mm
Collar diameter	... 40mm
Speeds (rpm)	... 5 (550-2500)
Swing	... 208mm
Spindle travel	... 50mm
Column diameter	... 46mm
Table size	... 160 x 160mm square
Motor	... 180W
Height	... 580mm
Nett/gross weight	... 21/23kg

Stock No.	Description	Euro each	GBP £ each
33662	230V Drill	N/a	N/a
65961	Chuck Guard	N/a	N/a
65969	Geared Chuck	N/a	N/a

DRAPER BULLETS

these need to be kept to a minimum, in order of priority.

- 13mm chuck capacity
- 0-45° tilting table
- Motor; 180W - 230VAC



Stock No.	Chk Digit	Description	FARNELL CODE
33662	3	5 SPEED 230V HOBBY BENCH DRILL	500859
65961	6	Chuck Guard	Ex Stock
65969	2	Geared Chuck	Ex Stock

BRAND: **DRAPER**

BARCODED **YES**