

Product data sheet

Specifications



Direct rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, for GS 50-63A IEC

GS1AH01

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	TeSys
Range	TeSys
Device short name	GS1AH
Product or Component Type	Rotary handle
Range compatibility	TeSys (TeSys GS) GS1 F TeSys (TeSys GS) GS1G
Type of operating handle	Direct right side
Handle colour	Black

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	50 A 63 A
Standards	IEC

Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3389110561111
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	5.51 in (14.0 cm)
Package 1 Weight	1.94 oz (55.0 g)

Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.79 lb(US) (1.266 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)