

6 ft USB to Parallel Printer Adapter - M/M

Product ID: ICUSB1284



The ICUSB1284 6 ft USB to Parallel Printer Adapter - M/M allows USB capable PCs to print to any standard parallel printer, converting a USB port into a Centronics (male) connector for direct connection to a parallel printer.

The USB interface provides a much faster data transfer rate than standard parallel ports, thereby reducing the time spent waiting for a print job or data transfer to be sent.

A portable, space-saving solution, the USB to Parallel Printer Adapter is self-powered and provides Plug and Play installation on Windows based, USB-compliant computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Allows you to quickly add a parallel port to your Windows computer

Features

- **USB TO PARALLEL:** The ICUSB1284 USB to Parallel printer adapter allows you to connect a 36-pin Centronics-equipped parallel printer to a computer via a USB-A 2.0 port
- **LOW POWER:** USB bus-powered operation, no external power adapter required (0.9W consumption, 5V at 0,18A)
- **SPECS:** USB-A male to 36-pin Centronics parallel male cable; 1.8m (6 ft) long; USB 2.0; Colour: Black; Material: Plastic; Chipset: Prolific PL2305
- **COMPATABILITY:** Provides Plug and Play installation on Windows based computers with USB; Supports Windows (incl. XP and up) Windows Server (2000 and up), Linux (2.6.X and up) and macOS 10.6 to 10.15, 11.0, 12.0, 13.0
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB to parallel cord is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	USB 2.0
Chipset ID	Prolific - PL2305

Performance

Maximum Data Transfer Rate	12 Mbps (1.5 MB/s)
----------------------------	--------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - Centronics (36 pin)

Software

OS Compatibility	Windows 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2000, 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 macOS 10.6 to 10.15, 11.0, 12.0, 13.0, 14.0 Linux 2.6.x and up - <i>LTS Versions only</i>
------------------	---

Power

Power Source	USB-Powered
Power Consumption (In Watts)	0.9W

Environmental

Operating Temperature	5C to 40C (41F to 140F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~80% RH non-condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	2.0 in [5 cm]
Product Height	0.7 in [1.7 cm]
Weight of Product	4.2 oz [118.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.0 in [26.0 mm]
Shipping (Package) Weight	4.8 oz [137.0 g]

What's in the Box

Included in Package	1 - USB to Parallel Converter Cable
---------------------	-------------------------------------

**Product appearance and specifications are subject to change without notice.*