

3ft (1m) Thunderbolt 4 Cable - 40Gbps - 100W PD - 4K/8K Video - Intel-Certified Thunderbolt Cable
- Compatible w/ USB4/Thunderbolt 3/USB 3.2/USB Type-C/DisplayPort

Product ID: TBLT4MM1M



This Thunderbolt 4 (40 Gbps) cable enables Thunderbolt 4 signals over USB Type-C connectors. Deliver video, data, and up to 100W of Power Delivery to Thunderbolt, USB, and DisplayPort devices.

This cable supports data transfer of 40 Gbps when connected to a Thunderbolt 4, Thunderbolt 3, or USB4-compatible source and device. It is capable of transferring photo and video files four times faster than standard USB 3.2 gen 2 (10Gbps) cables.

The Thunderbolt 4 cable is compatible with all USB Type-C devices and can be used to charge and sync mobile devices. In addition, this cable can be used to connect and power USB-C laptops, such as MacBook and Chromebook, and USB-C peripherals such as portable hard drives and docking stations.

The cable supports full-8K 60Hz video and DisplayPort 1.4a, and is compatible with DisplayPort displays. Use it to connect a docking station to laptop, or a laptop to a display

This Thunderbolt 4 cable delivers up to 100W of Power Delivery to charge a laptop or power a display, and 15W for bus-powered devices such as hard drive enclosures.

The cable can be used to daisy chain up to 6 Thunderbolt 4 enabled devices, such as laptops for peer-to-peer 10GbE networking. In addition, connect two Thunderbolt 4 laptops to transfer/migrate data.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE:** 3.3ft/1m Thunderbolt 4 cable supports 40 Gbps, 8K video, and 100W power; USB Type-C to Type C connectors offer universal compatibility with Thunderbolt 3 & 4, USB4, and other USB-C devices
- **THUNDERBOLT CERTIFIED:** Intel Thunderbolt certified for guaranteed compatibility with Thunderbolt hosts and devices; DisplayPort 1.4a with DSC supports up to 8K 60Hz or dual 4K 60Hz; Compliant with PCI Express 3.0 (32 Gbps) for external PCIe devices
- **QUALITY CONSTRUCTION:** Nickel-plated connectors with PVC strain reliefs for durability; Coaxial wire with braided alloy shield for enhanced EMI protection; Durable TPE outer jacket is environmentally friendly, non-toxic, halogen-free, and RoHS compliant
- **APPLICATIONS:** Versatile connectivity w/Thunderbolt 4 & USB-C laptops, M1/M2/M3 Pro/Max MacBooks, iPad Pro (5th gen and up), docks, 4K/8K UHD monitors, external PCIe chassis/storage drives; Low-latency performance w/Thunderbolt networking & audio devices
- **SPECS:** 3.3ft (1m); Black; Thunderbolt 4 (40 Gbps); USB4 (40 Gbps), USB 3.2 Gen 2 (10 Gbps); DisplayPort 1.4a w/ DSC; 8K 60Hz or Dual 4K 60Hz; PCIe 3.0; 100W PD; 30/34 AWG (Coaxial/Twisted Pair); Cable Outer Diam.: 0.18in (4.6mm)

Hardware

Warranty	2 Years
Active or Passive Adapter	Passive
	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers

Performance

Video Revision	DisplayPort 1.4
Maximum Data Transfer Rate	40 Gbps
Maximum Digital Resolutions	8K 60Hz
Type and Rate	Thunderbolt 4 - 40 Gbit/s
	Thunderbolt 3 - 40 Gbit/s
	USB 3.2 Gen 2 - 10 Gbit/s
	USB 3.0 - 5 Gbit/s

Connector(s)

Connector A	1 - Thunderbolt 4 (USB 4.0)
Connector B	1 - Thunderbolt 4 (USB 4.0)

Power

Power Delivery	100W
----------------	------

Environmental

Operating Temperature	10C to 40C (50F to 104F)
Storage Temperature	-10C to 50C (14F to 122F)
Humidity	85% RH

Physical Characteristics

Color	Black
Cable Length	3.3 ft [1 m]
Cable OD	0.2 in [4.6 mm]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.1 in [2.4 mm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	5.0 in [12.8 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	1.8 oz [52.0 g]

What's in the Box

Included in Package	1 - 1m Thunderbolt 4 USB-C Cable
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***