

## VDE 8098-160 H

### VDE Stripping pliers

with insulating sleeves

Code	ETIM
1552074	EC002109
EAN	UNSPSC
4010886815977	27-11-21-04
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



### Article description

- Opens automatically, with spring and adjusting screw
- V-shaped cutting jaws for stripping the plastic insulation of single- and multi-core conductors
- Easy adjustment to the required wire or strand diameter by means of the set screw and lock nut
- For wires from 0.8 to 6.0 mm<sup>2</sup>
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900

### Article information

Contents (Qty of pieces)	1	Width of head 1 [mm]	18,5 mm
Total length [mm]	160 mm	Standard	EN 60900/IEC60900
Material	Heat-treated steel	Jaw length L3 [mm]	43,5 mm
Handle design	2-component grips VDE insulated up to 1000 V.	Head thickness [mm] T1	8,5 mm
Surface	chrome-plated	Design non-sparking	No
Net weight [kg]	0,204 kg	Opening spring present	no
Total width [mm]	52 mm	Joint types	inserted joint
Total height [mm]	27 mm	Cable cross section [mm <sup>2</sup> ]	0,8-6,0