

IN 20 2

Screwdriver bit socket 1/4"

for in-hex screws

Code	ETIM
1812556	ECO02157
EAN	UNSPSC
4010886856383	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 6.3, ISO 1174, with ball retention groove
- Hand operated, knurled for good grip
- Chrome-plated
- Tip manganese-phosphated
- Chrome-vanadium steel

Article information

Contents (Qty of pieces)	1	Drive connector square female (metric)	6,3 mm
Total length [mm]	28 mm	Drive connector square female [inch]	1/4"
Material	Chrome-vanadium steel	Working length	28,0 mm
Surface	chrome-plated	Insert-Ø 1	12,0 mm
Net weight [kg]	0,01 kg	Tip length	16,0 mm
Total width [mm]	12 mm	Diameter 1 [mm]	12,0
Width across flats 1 [mm]	2	Insert Ø Actuator	12 mm
Standard	not standardised		