

60 S 10 JP

Single open ended spanner

adjustable

Code	ETIM
2171015	ECO02192
EAN	UNSPSC
4010886881583	27-11-17-26
Country of origin	eCl@ss
China	21-04-01-90
Customs tariff number	
82041200	



Article description

- Acc. to ISO 6787
- Jaw set at 15°
- Swedish pattern, roller with left hand thread
- With adjusting scale
- The protected mechanism and additional striking face allow light blows to be applied without impairing the function of the wrench
- Grip recess ensures secure hold - even with greasy hands
- Handy 2-component handle (JC and JP versions) for fatigue-free work
- Chrome-vanadium steel
- Design C = nickel and chrome plated, head ground
- Version P = manganese-phosphated, head ground
- Version PK = hook plastic coated
- Version JP and JC = additionally with plastic handle
- With hanging hole

Article information

Contents (Qty of pieces)	1	Clamping width [mm]	30 mm
Total length [mm]	255 mm	Graduation	0-30
Version/Execution	swedish model, roller with left-hand drive, version JP and JC = additionally with plastic handle	Total length [inch]	10
Material	Chrome-vanadium steel	Width across flats 1 [AF]	-
Surface	manganese phosphated	Jaw set	15°
Net weight [kg]	0,5 kg	Handle material	Plastic
Total width [mm]	70 mm	Ratchet function	no
Total height [mm]	20 mm	Suspension hole	yes
Standard	ISO 6787	Setting scale	yes