

7 R 36

Combination ratchet spanner

Flat pattern

Code	ETIM
2219557	ECO02176
EAN	UNSPSC
4010886883426	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



Article description

- With same size each end
- UD-Profile
- High torque transfer
- Chrome-vanadium steel 31CrV3
- Non-glare look due to matt chrome-plating, locking insert and pawl manganese-phosphated
- Hot forged
- Jaw: ground precisely to exact nominal size for optimum contact areas
- In combination with adaptor 7 RA or 7 RB (please order separately) the spanner 7 R can be used as a (bit) ratchet
- Hollow profile comfortable to hold
- Warp-resistant geometry with double T-girder effect
- For ratchet loosening and fast tightening
- Ring 13° offset from shaft, reversible

Article information

Contents (Qty of pieces)	1	Head height 1 [mm]	18,9 mm
Total length [mm]	470 mm	Width of head 1 [mm]	70,0 mm
Material	31CrV3	Width of head 2 [mm]	75 mm
Surface	chrome-plated	Standard	not standardised
Net weight [kg]	1,208 kg	Head height 2 [mm]	10,2 mm
Total width [mm]	74 mm	Jaw set	15°
Total height [mm]	20 mm	Return angle	5°
Width across flats [mm]	36,0		