

S 8393

Pliers set

3 pieces

Code	ETIM
3012859	EC011817
EAN	UNSPSC
4010886949719	27-11-32-01
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



Article description

- Practical set composition
- Consisting of power side cutter, power combination pliers, water pump pliers
- 8314-180 JC Power side cutter:
 - High force build-up due to convex handle shape and forwardly shifted pivot point in the joint
 - Induction-hardened cutting edges 63-65 HRC
 - Gedore special hardened and tempered steel, chrome-plated
 - 2K handle sleeves
 - Cutting capacity: 25mm²/AWG4. piano wire max. 2.0 mm. copper wire max. 6.00 m
- 8250-200 JC Power Combination Pliers:
 - For heavy continuous use
 - High force build-up due to the forward displacement of the pivot point in the joint
 - Induction hardened cutting edges 62-64 HRC
 - GEDORE special hardened and tempered steel, chrome-plated
 - 2K handle sleeves
 - Cutting capacity: 25mm²/AWG4. piano wire max. 2.0 mm. copper wire max. 6.00 mm
- 142 10 tsp water pump pliers:
 - Self-clamping gripping on pipes and nuts
 - 15-fold fine adjustment at the touch of a button
 - Good accessibility in narrow areas due to slim pliers head
 - Induction hardened teeth 61 HRC
 - Steel grey with blue dipped rough handles

Article parts list

Universal pliers No. 142 10 TL, 10" , 15-way adjustable dip-insulated, Power side cutter No. 8314-180 JC, 180 mm, 2-component handle, Power combination pliers No. 8250-200 JC, 200 mm, 2-component handle

Article information

Contents (Qty of pieces)	3	Standard	DIN ISO 5746 DIN ISO 5749 DIN ISO 8976 - Form C
Net weight [kg]	1,066 kg	Total depth [mm]	210 mm
Total width [mm]	210 mm	Design non-sparking	No
Total height [mm]	35 mm		