

1 B 10

Combination spanner with same size each end

metric

|                       |             |
|-----------------------|-------------|
| Code                  | ETIM        |
| 6000830               | EC002176    |
| EAN                   | UNSPSC      |
| 4010886600085         | 27-11-17-13 |
| Country of origin     | eCl@ss      |
| Germany               | 21-04-01-05 |
| Customs tariff number |             |
| 82041100              |             |



Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Sizes 5 and 5.5 mm with hexagon ring, up from size 6 mm with UD profile
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- \* not standardised

Article information

|                           |                       |                      |                                           |
|---------------------------|-----------------------|----------------------|-------------------------------------------|
| Contents (Qty of pieces)  | 1                     | Head height 1 [mm]   | 8,2 mm                                    |
| Total length [mm]         | 149 mm                | Width of head 1 [mm] | 15,5 mm                                   |
| Material                  | Vanadium steel 31CrV3 | Width of head 2 [mm] | 23,5 mm                                   |
| Surface                   | chrome-plated         | Standard             | DIN 3113 - Form B<br>ISO 3318<br>ISO 7738 |
| Net weight [kg]           | 0,042 kg              | Mouth position 1     | 15°                                       |
| Total width [mm]          | 23 mm                 | Head height 2 [mm]   | 4,7 mm                                    |
| Total height [mm]         | 15 mm                 | Height of offset 1   | 14 mm                                     |
| Width across flats 1 [mm] | 10                    | Ring offset          | 10°                                       |