

1 B 24

Combination spanner with same size each end

metric

Code	ETIM
6002370	EC002176
EAN	UNSPSC
4010886600238	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Sizes 5 and 5.5 mm with hexagon ring, up from size 6 mm with UD profile
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- * not standardised

Article information

Contents (Qty of pieces)	1	Width of head 1 [mm]	35,0 mm
Total length [mm]	320 mm	Width of head 2 [mm]	52 mm
Material	Vanadium steel 31CrV3	Standard	DIN 3113 - Form B ISO 3318 ISO 7738
Surface	chrome-plated	Mouth position 1	15°
Net weight [kg]	0,372 kg	Head height 2 [mm]	9,5 mm
Total width [mm]	49 mm	Height of offset 1	29,5 mm
Total height [mm]	30 mm	Ring offset	10°
Width across flats 1 [mm]	24	Weight	0,820 lbs
Head height 1 [mm]	15,5 mm		