

2 24X27

Double ended ring spanner

Code	ETIM
6018450	EC002188
EAN	UNSPSC
4010886601846	27-11-17-05
Country of origin	eCl@ss
Germany	21-04-01-06
Customs tariff number	
82041100	



Article description

- Acc. to DIN 838, ISO 3318, ISO 1085, ISO 10104
- Rings deep offset, strong but thin walls
- Vanadium steel 31CrV3, chrome-plated
- Satin non-glare finish
- Carefully forged and professionally machined:
- Ring: thin-walled, 5° deep offset from shaft, with UD profile for gentle transmission of force
- High bending strength - does not fracture or splinter when overloaded, thus minimising the risk of injury
- Overloading indicated by deformation
- For extremely deep or inset bolts
- Top-grade industrial quality for the hardest of continuous use

Article information

Contents (Qty of pieces)	1	Width across flats [mm]	24x27
Total length [mm]	340 mm	Width across flats 2 [mm]	27
Version/Execution	Rings deep offset, strong but thin walls	Head height 1 [mm]	14,4 mm
Material	31CrV3	Width of head 1 [mm]	35,7 mm
Surface	chrome-plated	Width of head 2 [mm]	40,1 mm
Net weight [kg]	0,506 kg	Standard	DIN 838 ISO 3310 ISO 1085 ISO 10104
Total width [mm]	40 mm	Head height 2 [mm]	15,4 mm
Total height [mm]	40 mm	Height of offset 1	34,5 mm
Width across flats 1 [mm]	24	Ring offset	5°