

2 27X30

Double ended ring spanner

| | |
|-----------------------|-------------|
| Code | ETIM |
| 6018960 | EC002188 |
| EAN | UNSPSC |
| 4010886601891 | 27-11-17-05 |
| Country of origin | eCl@ss |
| Germany | 21-04-01-06 |
| Customs tariff number | |
| 82041100 | |



Article description

- Acc. to DIN 838, ISO 3318, ISO 1085, ISO 10104
- Rings deep offset, strong but thin walls
- Vanadium steel 31CrV3, chrome-plated
- Satin non-glare finish
- Carefully forged and professionally machined:
- Ring: thin-walled, 5° deep offset from shaft, with UD profile for gentle transmission of force
- High bending strength - does not fracture or splinter when overloaded, thus minimising the risk of injury
- Overloading indicated by deformation
- For extremely deep or inset bolts
- Top-grade industrial quality for the hardest of continuous use

Article information

| | | | |
|---------------------------|--|---------------------------|--|
| Contents (Qty of pieces) | 1 | Width across flats [mm] | 27x30 |
| Total length [mm] | 356 mm | Width across flats 2 [mm] | 30 |
| Version/Execution | Rings deep offset, strong but thin walls | Head height 1 [mm] | 15,4 mm |
| Material | 31CrV3 | Width of head 1 [mm] | 40,1 mm |
| Surface | chrome-plated | Width of head 2 [mm] | 44,1 mm |
| Net weight [kg] | 0,628 kg | Standard | DIN 838 ISO 3310 ISO 1085 ISO 10104 |
| Total width [mm] | 44 mm | Head height 2 [mm] | 16,4 mm |
| Total height [mm] | 42 mm | Height of offset 1 | 35,5 mm |
| Width across flats 1 [mm] | 27 | Ring offset | 5° |