

6 16X17

Double open ended spanner

metric

Code	ETIM
6066260	ECO02130
EAN	UNSPSC
4010886606629	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-04
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

Article information

Contents (Qty of pieces)	1	Width across flats [mm]	16x17
Total length [mm]	205 mm	Width across flats 2 [mm]	17
Material	31CrV3	Head height 1 [mm]	6 mm
Net weight [kg]	0,128 kg	Width of head 1 [mm]	35,5 mm
Total width [mm]	39 mm	Width of head 2 [mm]	38,5 mm
Total height [mm]	6 mm	Standard	DIN 3110 ISO 3318 ISO 1085 ISO 10102
Width across flats 1 [mm]	16	Mouth position 1	15°