

## 6 17X19

### Double open ended spanner

metric

Code	ETIM
<b>6066420</b>	<b>ECO02130</b>
EAN	UNSPSC
<b>4010886606643</b>	<b>27-11-17-06</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-01-04</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

### Article information

Contents (Qty of pieces)	1	Width across flats [mm]	17x19
Total length [mm]	221 mm	Width across flats 2 [mm]	19
Material	31CrV3	Head height 1 [mm]	6,5 mm
Net weight [kg]	0,168 kg	Width of head 1 [mm]	38,5 mm
Total width [mm]	43 mm	Width of head 2 [mm]	43 mm
Total height [mm]	7 mm	Standard	DIN 3110 ISO 3318 ISO 1085 ISO 10102
Width across flats 1 [mm]	17	Mouth position 1	15°