

6 19X22

Double open ended spanner

metric

Code	ETIM
6066770	ECO02130
EAN	UNSPSC
4010886606674	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-04
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

Article information

Contents (Qty of pieces)	1	Width across flats [mm]	19x22
Total length [mm]	235 mm	Width across flats 2 [mm]	22
Material	31CrV3	Head height 1 [mm]	7 mm
Net weight [kg]	0,219 kg	Width of head 1 [mm]	43,0 mm
Total width [mm]	48 mm	Width of head 2 [mm]	48,5 mm
Total height [mm]	7 mm	Standard	DIN 3110 ISO 3318 ISO 1085 ISO 10102
Width across flats 1 [mm]	19	Mouth position 1	15°