

6 24X27

Double open ended spanner

metric

Code	ETIM
6067580	ECO02130
EAN	UNSPSC
4010886606759	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-04
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

Article information

Contents (Qty of pieces)	1	Width across flats [mm]	24x27
Total length [mm]	264 mm	Width across flats 2 [mm]	27
Material	31CrV3	Head height 1 [mm]	8 mm
Net weight [kg]	0,337 kg	Width of head 1 [mm]	53,5 mm
Total width [mm]	58 mm	Width of head 2 [mm]	60 mm
Total height [mm]	8 mm	Standard	DIN 3110 ISO 3318 ISO 1085 ISO 10102
Width across flats 1 [mm]	24	Mouth position 1	15°