

19 25

Socket 1/2"

hexagon UD profile

Code	ETIM
6131930	EC002203
EAN	UNSPSC
4010886613191	27-11-17-04
Country of origin	eCl@ss
Germany	21-04-02-18
Customs tariff number	
82042000	



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

Article information

Contents (Qty of pieces)	1	Standard	not standardised
Total length [mm]	41 mm	Drive connector square female (metric)	12,5 mm
Material	Chrome-vanadium steel	Drive connector square female [inch]	1/2"
Surface	polished, chrome-plated	Working length	41,5 mm
Net weight [kg]	0,139 kg	Insert-Ø 1	34,2 mm
Total width [mm]	34 mm	Insert-Ø 2	28,8 mm
Total height [mm]	34 mm	Operating depth	18,5 mm
Width across flats 1 [mm]	25		