

IN 19 19

Screwdriver bit socket 1/2"

for in-hex screws

Code	ETIM
6154120	ECO02157
EAN	UNSPSC
4010886615416	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- No. IN 19 17 for oil filter and drain plug screws

Article information

Contents (Qty of pieces)	1	Width across flats l [mm]	19
Total length [mm]	60 mm	Standard	not standardised
Material	Chrome-vanadium steel	Drive connector square female (metric)	12,5 mm
Surface	chrome-plated	Drive connector square female [inch]	1/2"
Net weight [kg]	0,222 kg	Working length	40,0 mm
Total width [mm]	30 mm	Tip length	20,0 mm
Total height [mm]	30 mm	Insert Ø Actuator	27 mm