

ITX 19 T40

Screwdriver bit socket 1/2"

for recessed TX screws, short

| | |
|-----------------------|-------------|
| Code | ETIM |
| 6156330 | ECO02213 |
| EAN | UNSPSC |
| 4010886615638 | 27-11-17-01 |
| Country of origin | eCl@ss |
| Germany | 21-04-04-02 |
| Customs tariff number | |
| 82079030 | |



Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish

Article information

| | | | |
|---------------------------|-----------------------|--|-------------------------------|
| Contents (Qty of pieces) | 1 | Total height [mm] | 23 mm |
| Total length [mm] | 55 mm | Standard | DIN 3120 - C 12,5 ISO 1174 |
| Material | Chrome-vanadium steel | Drive connector square female (metric) | 12,5 mm |
| Tip size TX (recess) | T40 | Drive connector square female [inch] | 1/2" |
| Tip size TX (recess) [mm] | 6,65 mm | Tip length | 17,0 mm |
| Surface | chrome-plated | Insert Ø Actuator | 22,5 mm |
| Net weight [kg] | 0,076 kg | Screw size | M7 - M8 |
| Total width [mm] | 23 mm | | |