

ITX 19 T60

Screwdriver bit socket 1/2"

for recessed TX screws, short

Code	ETIM
6158540	EC002213
EAN	UNSPSC
4010886615850	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish

Article information

Contents (Qty of pieces)	1	Total height [mm]	25 mm
Total length [mm]	56 mm	Standard	DIN 3120 - C 12,5 ISO 1174
Material	Chrome-vanadium steel	Drive connector square female (metric)	12,5 mm
Tip size TX (recess)	T60	Drive connector square female [inch]	1/2"
Tip size TX (recess) [mm]	13,25 mm	Tip length	15,0 mm
Surface	chrome-plated	Insert Ø Actuator	24,7 mm
Net weight [kg]	0,137 kg	Screw size	M14
Total width [mm]	25 mm		