


20 13

Socket 1/4"

hexagon

Code	ETIM
6166640	EC002203
EAN	UNSPSC
4010886616666	27-11-17-04
Country of origin	eCl@ss
Taiwan	21-04-02-18
Customs tariff number	
82042000	



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 6.3, ISO 1174, with ball retention groove
- Hand operated, knurled for good grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated

Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 ISO 2725-1 DIN 3120 - C 6,3 ISO 1174
Total length [mm]	25 mm	Drive connector square female (metric)	6,3 mm
Material	Chrome-vanadium steel	Drive connector square female [inch]	1/4"
Surface	Matt chrome-plated	Working length	25,0 mm
Net weight [kg]	0,03 kg	Insert-Ø 1	18,5 mm
Total width [mm]	18 mm	Insert-Ø 2	18,5 mm
Total height [mm]	18 mm	Operating depth	10,0 mm
Width across flats 1 [mm]	13		