

2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch – USB Powered

Product ID: SV211HDUA



The SV211HDUA 2-Port HDMI Cable KVM Switch with Audio and Remote Switching Control lets you control two HDMI, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact HDMI USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the HDMI KVM switch is USB-powered.

This KVM with HDMI video capability offers support for 1080p HD resolutions (up to 1920x1200) for the ability to drive a large HDMI display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice

- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

Features

- Supports HD resolutions (1080p - 1920x1200)
- Switch PCs via push-button, hot-keys or switching software
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac platforms
- USB Powered - No external power adapter required
- Analog (3.5mm) and HDMI audio supported
- Independent audio/mic switching for uninterrupted audio
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	HDMI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Industry Standards	HDCP
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Audio Specifications	3.5mm and HDMI audio supported
Port Selection Support	Push Button, Hotkeys, and Software

Connector(s)

Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) 1 - HDMI (19 pin) 2 - USB 2.0 Type-A (4 pin, 480Mbps)
Host Connectors	2 - 3.5 mm Mini-Jack (3 Position) 1 - HDMI (19 pin) 1 - USB 2.0 Type-A (4 pin, 480Mbps)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022 Mac OS 10.6 to 10.12
------------------	--

Special Notes / Requirements

Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
------	--

Indicators

LED Indicators	1 - PC Selection indicator
----------------	----------------------------

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (4F to 140F)
Humidity	0~90% RH Non-Condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	33.5 in [850 mm]
Product Length	3.5 in [8.8 cm]
Product Width	2.6 in [6.6 cm]
Product Height	0.9 in [2.3 cm]
Weight of Product	12.4 oz [350.0 g]

Packaging Information

Package Quantity	1
Package Length	9.7 in [24.6 cm]
Package Width	6.4 in [16.2 cm]
Package Height	2.5 in [6.4 cm]
Shipping (Package) Weight	1.0 lb [0.5 kg]

What's in the Box

Included in Package	1 - KVM Switch
	1 - Software CD
	1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***