


BEST SELLER



ABMM-A-C Cable Tie Mount, White, ABS, Rubber Adh., 0.75x0.75", PK100

ABMM-A-C

Panduit's ABMM-A-C rubber-based adhesive back cable tie mounts have been designed for fast installation and long-term performance. These mounts can be used with miniature and intermediate cables ties. Made of ABS plastic and intended for use in indoor environments. They are 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 100.

Specifications

Product Type	Cable Tie Mount
Color	White
Environment	Indoor
Material	ABS
Maximum Compatible Panel Thickness (In.)	0.04
Maximum Compatible Panel Thickness (mm)	1
Maximum Operating Temperature (°C)	49
Maximum Operating Temperature (°F)	120
Minimum Operating Temperature (°C)	-29
Minimum Operating Temperature (°F)	-20
Mount Method	Rubber Adhesive Tape
Overall Height (In.)	0.18
Overall Height (mm)	4.6
Overall Length (In.)	0.75
Overall Length (mm)	19.1
Overall Width (In.)	0.75
Overall Width (mm)	19.1
Standards Met	CE Compliant, UL Recognized: E136577, RoHS Compliant
Static Load Capacity (kg)	0.136
Static Load Capacity (lb)	0.3
For Use With	Miniature, Intermediate Cross-Section Ties

Packaging Detail

UPC	07498358500
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0266
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.1329