


## **SMBM-BNCM174XX**

(Cable Assembly Coaxial SMB Male to BNC Male RG-174)





Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

**Electrical Ratings**Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

| Connector | Cable  | Connector | Frequency | VSWR |
|-----------|--------|-----------|-----------|------|
|           |        | Impedance | (GHz)     |      |
|           |        | (Ohms)    | , ,       |      |
| SMB       | RG-174 | 50        | 0-3       | 1.35 |
|           |        |           |           | MAX  |
| BNC       | RG-174 | 50        | 0-3       | 1.35 |
|           |        |           |           | MAX  |

## **Product Attributes**

| Gender                | Male to Male                      |  |
|-----------------------|-----------------------------------|--|
| Style                 | SMB to BNC                        |  |
| 1st Connector         | Gold Plated SMB Male Plug w/ PTFE |  |
|                       | Insulator                         |  |
| 2nd Connector         | Gold Plated BNC Male Plug w/ PTFE |  |
|                       | Insulator                         |  |
| Features              | Shielded                          |  |
| Operating Temperature | -65°C (-85°F) to 145°C (293°F)    |  |
| SMBM-BNCM17405        | 0.5M                              |  |
| SMBM-BNCM17410        | 1M                                |  |
|                       |                                   |  |
| RoHS 3 Compliant      |                                   |  |

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524