

PZ 2.5 S

0.14mm², 2.5mm², Trapezoidal crimp

Item No. **2903690000**



Properties

General ordering data

Version	0.14mm², 2.5mm², Trapezoidal crimp
Order No.	2903690000
Type	PZ 2.5 S
GTIN (EAN)	4099986027008
Qty.	1 items

Dimensions and weights

Depth	31 mm
Depth (inches)	1.22 inch
Height	70 mm

Height (inches)	2.756 inch
Width	160 mm
Width (inches)	6.299 inch
Net weight	290.6 g

Technical data



Version	Mechanical, without interchangeable inserts
---------	---

Description of contact



Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 26
Crimping range, max.	2.5 mm ²
Crimping range, min.	0.14 mm ²
Type of contact	Wire-end ferrules with/without plastic collars

tool data crimping



Crimping type/profile	Trapezoidal crimp
Wire end ferrules cross-section, max.	2.5 mm ²
Wire end ferrules cross-section, min.	0.14 mm ²

Downloads



User Documentation	BDAL PZ 2.5
Catalogues	Catalogues in PDF-format

Classifications



ETIM 6.0	EC000168
ETIM 7.0	EC000168
ETIM 8.0	EC000168
ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11

