

Dual Range Precision Sound Level Meter



Precision sound level meter ideal for measuring noise levels in different environments and industries. Manufactured to IEC651 Type 2, this meter is lightweight, easy to use both internally and externally.

- Selectable A or C frequency weightings
- Slow or Fast response readings and Max Hold
- Fast response gives readings to all detected noise levels
- Min/Max memory displays highest and lowest dB measured values
- User calibration via internal oscillator at 94dB
- Standard 4mm camera bush for tripod mounting
- Supplied in a hard carry case with a battery, wind muffler and instructions for use

Range	35-90dB(low), 75-130dB(high)
Resolution	0.1dB full range
Accuracy	±1.5dB
Dynamic Range	55dB
Operation	0°C to 50°C, below 90% RH

339940.275815

Order Code

499-0237