

### Part Number : 02092103

Product Description : 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Bag Series Number : 1190 Status : Active Product Category : Crimp Terminals Engineering Number : 1190-(P901)L Packaging Alternative : 0002092101 (Reel)



### **Documents & Resources**

#### Drawings

Drawing 002092103\_sd.pdf Packaging Design Drawing PK-1190-003-001.pdf

### Specifications

Packaging Specification PK-1190-001-001.pdf Product Specification PS-02-09-001.pdf Test Summary 11890000-TS-000.pdf

## **Product Environment Compliance**

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	®
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

# Part Details

### General

Status	Active
Category	Crimp Terminals
Series	1190
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 14-20 AWG, Bag
Application	Power, Wire-to-Wire
Product Family	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	800753746107

# Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.312/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size (AWG)	14, 16, 18, 20

Wire Size mm <sup>2</sup> N/A
-------------------------------

## Solder Process Data

Lead-Free Process Capability	N/A	
------------------------------	-----	--

# Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	<u>1261</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1292</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1396</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1490</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1545</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1619</u>

# Application Tooling

## Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	0011020003
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>0011030006</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 14-24 AWG	<u>0638111000</u>
PremiumGrade Hand Crimp Tool for Standard .093" and .125" Pin and Socket Terminals	0638191100
Extractor Tool for .093 and HCS-125 Product Series	0638240200

This document was generated on Feb 26, 2024