

# Han D F Crimp Contact Ag AWG 16



Part number	09 15 000 6201
Specification	Han D F Crimp Contact Ag AWG 16
HARTING eCatalogue	https://b2b.harting.com/09150006201

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

#### Technical characteristics

Conductor cross-section	1.5 mm²
Conductor cross-section	AWG 16
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm
Mating cycles	≥500

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

# Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

### Commercial data

100
0.5 g
Germany
35366990
5713140022041
EC000796
27440204 Contact for industrial connectors
3