

SSHB10H-R17055

Aliases (UALSB1R1705500)

KEMET, SSHB10H, AC Line Filters, Dual Mode, 5.5 mH



Click [here](#) for the 3D model.

Dimensions

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm NOM
Wire Size	0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Component Weight	10 g

General Information

Series	SSHB10H
Style	Through-Hole
RoHS	Yes
Notes	Marking: R17 Lot No.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	5.5 mH (10 kHz)
Current	1.7 A
Temperature Range	-25/+120°C
DC Resistance	190 mOhms