



Click [here](#) for the 3D model.

### Dimensions

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm NOM
Wire Size	0.37mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Component Weight	10 g

### General Information

Series	SSHB10HS
Style	Through-Hole
RoHS	Yes
Notes	Marking: R13 Lot No.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	7.1 mH (10 kHz)
Current	1.3 A
Temperature Range	-25/+120°C
DC Resistance	250 mOhms