



Click [here](#) for the 3D model.

### Dimensions

L	5.3mm +/-0.2mm
W	5mm +/-0.2mm
T	3mm MAX
LL	1mm NOM
G	2.5mm +/-0.2mm

### Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	2500

### General Information

Series	MPX
Style	SMD
Chip Size	0530(2120)
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.

### Specifications

Inductance	10 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	3.1 A (Irms, 40C Rise By Self Heating), 2.5 A (Isat, 20% Drop In Inductance), 3.5 A (Isat, 30% Drop In Inductance)
DC Resistance	140.1 mOhms
Self-Resonant Frequency	18 MHz