









Circuit



Technical Data:

Case Material:Cover:.....Vyncolit black
Base Plate:.....PA GF black
Switch Lever Material:.....PA GF red
Min. Insulation Resistance:.....100MOhm
Dielectric Withstanding Voltage:.....1050V-1min
Max. Contact Voltage Drop:.....150mV
Voltage:.....up to 32VDC
Continuous Rating:.....2x500A
Overload:.....2x2000A-1.5min
.....2x2500A-10sec
Sealing:.....IP 67/IEC 529
Vibration:.....10G 18-500Hz
Weight:.....860g / 1.9Pound
Temperature Range:.....-40°C to +85°C
Wire Section(at nominal load):.....min.250mm2
Key:.....not removeable
Max. Tourque (Main Contacts)15-20Nm

	Date	Name	mm	Scale		Drawing No:
Drawn	02.10.2008	Seege		1:2		35-523-251-R
Check	23.03.2017	Grind		General Tolerances DIN ISO 2768 cL		NSN: