



Click [here](#) for the 3D model.

### Dimensions

D	15mm MAX
T	8.5mm MAX
LL	15mm +/-2mm
S	6mm
S1	8mm
Wire Size	0.3mm

### Packaging Specifications

Packaging	Bulk
Packaging Quantity	3000
Typical Component Weight	2 g

### General Information

Series	SC-G/GS
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	1 mH (1 kHz)
Current	1 A
Temperature Range	-40/+105°C
DC Resistance	130 mOhms