



General Information

Series	SU-10VFC-R
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	1900 μ H
Current	1.5 A
Temperature Range	-25/+120°C
DC Resistance	0.24 Ohms

Click [here](#) for the 3D model.

Dimensions

L	18mm MAX
T	15.5mm MAX
H	15mm MAX
LL	3.5mm +/-0.7mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.37mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	700
Typical Component Weight	6.5 g