

# R13 Round Rocker Switches 10A 250Vac

rocker switches



- ▶ Miniature round rocker switch
- ▶ Ratings up to 10A, 250Vac
- ▶ Single & double pole
- ▶ Illuminated & non-illuminated, neon and LED
- ▶ Choice of actuators
- ▶ Matching indicator
- ▶ Panel cut out: 20.2 dia.



**SP 10(4)A 250Vac T85**

**DP 10(4)A 250Vac T85**



**UL CSA SP 16A 125Vac & 10A 250Vac**  
**UL CSA DP 16A 125Vac, 10A 250Vac, 10A 28Vdc**  
**UL 85°C, file E67774(S), CSA file LR45128**



**RoHS compliant**

Single pole has  $\mu$  contact gap. Technical data on pages 4 & 5.

**Special products**

Are made to order and can be supplied with a range of body and rocker/lens colours, print & lamp voltage.  
 Call sales for availability to your special requirements.

## R13 112A AAA


TERMINAL FUNCTION ROCKER BODY PRINT, COLOUR, VOLTAGE ETC

### PRODUCT DETAILS



SP ON - OFF  $\mu$

**Cat no.**  
**R13 112A AAA**




SP ON - OFF  $\mu$   
Lit 230V

**Cat no.**  
**R13 112B NAC**




SP ON - OFF  $\mu$

**Cat no.**  
**R13 112A AAB**




SP ON - ON  $\mu$

**Cat no.**  
**R13 112C AAA**




SP ON - OFF  $\mu$   
Lit 230V

**Cat no.**  
**R13 112B NAA**



SP ON - OFF - ON  $\mu$

**Cat no.**  
**R13 112D AAA**



SP ON - OFF  $\mu$   
Lit 230V

**Cat no.**  
**R13 112B NAB**



SP ON - OFF  $\mu$   
(Momentary ON)

**Cat no.**  
**R13 208F AAA\***



DP ON - OFF

**Cat no.**  
**R13 244A AAA**




DP ON - OFF  
Lit 230V

**Cat no.**  
**R13 244B NAA**


### DIMENSIONS (mm)

#### Panel cut-out




Snap fixing into panel thickness up to 3.0

#### Single pole



\* R13 208F has 12.5mm deep body

#### Double pole





R13 112B NAA



R13 112A AAA




R13 112A2 ---

rocker  
switches


**PRODUCT  
DETAILS**




SP ON - OFF μ  
Bright colour ON signal  
**Cat no.**  
**R13 112A2 - -**




SP ON - OFF μ  
Lit Window  
**Cat no.**  
**R13 112B2 - -**



SP ON - OFF μ  
Paddle tip has red LED  
**Cat no.**  
**R13 112LP - -**




Indicator light  
**Cat no.**  
**R9 92B - - -**



approvals - contact sales

**PANEL CUT-OUT (mm)**



Snap fixing into panel thickness up to 3.0



**Protective cover L188**

Snaps on to bodies (not R13 211 or R13 112LP), this reduces maximum acceptable panel thickness to 2.4mm.