



Catalogue 2024

Europe's Widest Quality Range of Stapling and Nailing Products

Europe's Widest Quality Range of **Stapling and Nailing Products**

Contents

Pages

Tacwise Story	6 – 7
New Products	8 – 9

Hand Tackers 10 – 29

Z2 Lightweight	10 – 11
Z2 53-13M All Metal	12 – 13
Z4-140 (4-in-1)	14 – 15
Z5-53 (5-in-1)	16 – 17
Z-CT Duo Cable Tacker	18 – 19
Hammer Tackers	20 – 21
Hammer Tacker Bundles	22
Staple Remover	23

13, 140, 53, 71 & 91 Tools – Features, Applications & Specifications 24 – 27

Cordless Staple/Nail Guns 28 – 37

Hobby 53-13EL 4V	28 – 29
------------------	---------

- 140 and 53-13EL 12V 30 31
- 12V 191 Cordless Staple/Nail Gun 32 33
- 20V 191 Cordless Staple/Nail Gun 34 35
 - Ranger EL-PRO 18V 36 37

Corded Electric Staple & Nail Guns 38 – 47

- Compact Electric Tackers 38 39
- Medium Duty Electrics 181ELS & 191EL Pro 40 41
 - Heavy Duty Electrics Duo 35 & 18G/50 42 43
 - Heavy Duty Electrics 400ELS Pro 44 45
- Cordless & Corded Electric Tools Features, Applications & Specifications 46 47
 - Staple Families at a Glance 48 49



Pages

Hand & Electric Staple & Nail Guns – Staples & Nails	50 – 5 3
Hot & Cool Melt Glue Guns	54 – 57
Cordless Glue Guns Corded Glue Guns Glue Guns & Glue Sticks – Features, Applications & Specifications	54 – 55 56 57
Air Stapling	58 – 66

General Purpose & Upholstery Staple Guns	60 -	- 62
General Purpose & Upholstery Staple Guns – Staples	62	
Narrow Crown Staplers	63	
Narrow Crown Staplers & Corrugated Fasteners – Staples	64	
	05	~~~

Heavy Duty & Wide Crown Staplers & Corrugated Fastener 65 – 66

Air Nailing 67 – 85

	71
Nails, Brads & Finish Nails 70 –	
Coil Nailers 72 –	77
Coil Nailers – Nails 78	
Strip Nailers 79 –	80
Strip Nailers – Nails 80	
Variations of Air Tool Triggers. Choosing The Correct Fastening Length 81	
Air Tools – Features, Applications & Specifications 82 –	85

Browse by Project	86 – 87
Key & Conversion Chart	88

Our Story

User comfort, performance and best value

With a wealth of industry experience, Tacwise delivers the most complete range of quality stapling and nailing products, from DIY through to all-professional models and consumables.

Using our extensive knowledge, we build class-leading tools and fasteners for world markets with a focus on user comfort, performance and best value.

Productivity and satisfaction are at the very heart of our mission, enabling users to do and achieve more. Our cordless tools are perfect for convenience without the hassle of wires or cables.



Care for the environment

We're stripping out single-use plastic without compromising on protective packaging and we plan to do much more. We'll accelerate our efforts to find more, new ways to reduce, reuse and recycle.

Our tools can be easily disassembled to allow for specific recycling, an example being our tackers, which are screwed together whilst others are mostly welded or pressed together.

Products are designed to achieve strength and longevity through carefully selected materials.

Our worldwide customers expect us to make our designs, developments, manufacturing processes and products as energy efficient and environmentally responsible as possible. It is a continuing mission.

> Like quality, environmental management is a journey without a destination. We have to think globally and act locally. After all, we are all in this together.





Repair, reuse and recycle

We must all be more responsible and shift away from the global 'throw away' society. At Tacwise we have made it easy and inexpensive to service our air tools by yourself. Simply follow the step-by-step video instructions and quickly identify and purchase the parts you need from Tacwise.com.



Our Germ-Savvy[®] antimicrobial agent is added to external plastic parts during manufacture to provide protection for the lifetime of the product. It kills up to 99% of bacteria. It's ISO certified, making it highly credible. With no price premium

Look for the Germ-Savvy symbol throughout this catalogue.

Europe's widest quality range

Tacwise has the widest quality stapling, nailing and gluing programme to tackle virtually every fastening challenge.

The dominant brand associated with hand and electric stapling/nailing tackers within the UK market. We have the widest range of quality industrial fastenings and pneumatic tackers in Europe and 60+ years of knowledge and experience. Utilising all of our expertise we continue to create class leading tools and fasteners for the whole of Europe and beyond.

NEW 61 New Products

Constantly searching for better consumer solutions, once again we are proud to present some very exciting new products for 2024. Powerful and with great user features we lead with the Z2 family of hand tackers and have refreshed our larger models with the Z4 and Z5 ultra lightweight tools. As well as a rather special cable tacker, the Z-CT Duo. Each of these are bringing something quiet new to the market place.

We are also introducing two excellent cordless staplers/nailers with a 12V or 20V battery, capable of firing 91 Series staples and 180 (18G) nails. Dovetailing into this is our new 20V safety battery, with includes a dedicated on/off safety switch and is fast charging.

More information and imagery can be found in the relevant pages of this catalogue.

Hand Tackers

We've added 2 new lightweight additions to the Z2 range, plus our 2 professional Alu stapler/nailers (Z4 and Z5). And Z-CT Duo cable tacker.

8 new items



Hammer Tackers

Offering exceptional value, these hammer tackers are supplied in bundles with up to 75,000 staples.



Corded Electric Tools

Presenting 2 new compact corded tools packed with features and 4 new bundles with fastenings included.

6 new items

Staples

Made from high grade raw materials that always deliver outstanding results. With 3 new additions to our staple range you'll find what you need with ease.

3 new items





Cordless Staple/Nail Guns

The new cordless Master Nailer[™] range provides speed, precision and versatility for a wide range of fixing applications.



Cordless Glue Guns

2 new 12V hot melt glue guns, 1 for 12mm glue sticks and a new variation of the 12V 7mm gun.

2 new items



Air Stapling & Nailing

7 new reliable and versatile products, including the 90mm coil nailer and 90mm 21° inclined strip nailer.

7 new items



Staple/Nail Selection Packs

3 new handy selection packs all supplied in resealable clams to keep your staples and nails organised.



Brad & Finish Nails

New pack sizes for the ever-popular 18G nails and new reusable storage boxes for our 15G finish nails.



Coil & Strip Nails


Our 4 new stainless steel coil nails are ideal for external applications with long-lasting corrosion protection. Plus 6 new strip nails.



Hand Tackers **Z** Series

Loaded with features

Tacwise incorporate many great features into our hand tackers, making these high quality dependable tools a pleasure to use. The Less Effort feature avoids the uncomfortable 'snap' when firing and reduces hand strain. All models include a bottom loading magazine for hassle-free use, along with a lock-down handle and staple viewing window as standard. In addition, all our tackers are designed for disassembly – making them easy to recycle.







Z2 53-13T Staple Tacker 53/4-8mm



13/4-8mm

Stylish, compact and lightweight. Built for the professional and hobby user. The frosted transparent design is paired with outstanding engineering. Takes the very popular 53 & 13 series staples.

Replaces code: 0858



Berson Window

Z2 53-13L Lightweight 1


Perfect for DIY

Powerful and super lightweight. At just 0.18kg, this polymer-bodied tool is tough yet comfortable to use for long periods of time.

Attention to the detail

At Tacwise we pride ourselves on adding details and features to our tools that benefit and enhance the user experience.





No Loose Feeder

Professional Code: 1727 53 Staples 4-8mm (Capacity 105)

Bottom Loading



13 Staples 4-8mm (Capacity 110)





Includes: 300pcs 53 staples

Trade = 6 Units Transit = 36 Units

Z2 53-13M All Metal Staple Tacker

For professional and serious DIY

This all metal aluminium bodied tool is lightweight and durable. Fires both 53 and 13 series staples without any need for adjustment. Requires very little firing pressure.



Jock-Down Handle

(53/4-8mm) (13/4-8mm) (140/4-8mm) (53F/4-8mm)







TACWIS

A great feature aiding the accurate placement of staples. The margin guide is completely adjustable, it also has the added benefit of being removable when not required. The Z2 tacker has a metal outer body and a full-steel chassis, with a hardened steel magazine rail to avoid wear as the staple strip travels.




Z4-140 4-in-1 Tacker ໜ

right Aluminium Die Case

uuuu

Professional with a narrow crown staple option

This powerful yet lightweight aluminium-bodied tool can fire 4 different types of fastenings without any need for adjustment. This is the first hand tacker on the market which features the option of using the professional narrow crown gimping staple (91 Series), making it perfect for a variety of professional tasks that require a more discreet staple finish.



Staple, Mindow

The Z4 takes the professional 140 staple as well as three other types of fastener – the 91 series staple, the 180(18G) nail and 180 headless pin. It's easy to swap between all of these fasteners, making this a versatile tool for any tradesperson.

140 91 Staples 6-14mm

4-in-7

140 197

186/ 180 180 Headless Nails 10-15mm

POWAL

Adjuster

Down Handle





Z4-140 4-in-1 Metal Staple/Nail Tacker

140/6-14mm 91/6-14mm 180(18G)/10-15mm 180/15mm headless



This versatile staple and nail gun is suitable for carpets and underlay, netting and wire fencing, plastic sheeting, breather membrane, insulation and many more. Perfect for the flooring trade as it combines the common 140 staple and 91 gimping staple within one tool. Replaces codes: 0806 / 0807

Hand Tackers Stapling up to 14mm / Nailing up to 15mm

Fires Five Different Types of Fastener

A fantastically versatile tacker firing five types of fastener without need for adjustment, including three types of staple, a brad nail and a headless pin.

6

Lukas

5-in-1 Ultimate Versatility

The first all professional tool to take three variations of staple including the important 71 type upholstery staple.



K



18G/180 180 Headless

Nails 10-15mm

AC





Z5-53 5-in-1 Tacker 🔊

Professional staple & nail gun with a specialist upholstery staple option

Powerful and ultra lightweight as just 0.64kg (1.4lb), this aluminium-bodied tool is perfect for professional trades and serious DIYers wanting a comfortable, easy to use tool for an enormous range of applications.



Suitable for upholstery, picture framing, display/shop fitting, fabrics and blinds, hobby crafts, theatre/film scenery and many more. Replaces codes: 0880 / 0808 / 0881

Z-CT Duo Cable Tacker ໜ

Professional tacker for securing both 4.5mm & 6mm cables

Just like Z4 and Z5 staple tackers, the Z-CT Duo is built from super-lightweight aluminium and weighs in at just 0.6kg (1.3lb). Switching between staple sizes and lengths does not require any adjustment and there is a pressure control to assist when stapling into hard or soft wood. Perfect for a wide variety of professional low voltage cabling tasks that require precision. Uses the most advanced die-casting methods, meaning this tool has fewer moving parts for increased reliability.



Ultimate Low Voltage Cable Fixing

The first ultra lightweight all-professional tool for many staple variations.









Hammer Tackers

For high volume fixing tasks

Built without compromise, our hammer tackers are designed to offer the very best in speed and performance. The perfect solution to many fixing tasks, from roofing to flooring. Tacwise all-metal hammer tackers, continue to meet the needs of a diverse range of trades.

A19

A19 (53 & 13 Type) Hammer Tacker 53/6-10mm 13/6-10mm

Professional	Code: 1	327	
53 Staples 6-10m (Capacity 120) 13 Staples 6-10m (Capacity 120)		Hanging Retail Box	Trade = 1 Unit Transit = 20 Units

This compact model takes both the popular 53 and 13 series staples from 6mm to 10mm without the need for any adjustment. A fast and easy way to deal with tasks where many staples are fired in a short time such as securing plastic sheeting. 53 series staples are now available in stainless steel for exterior applications.









Lough Construction

TACHISE HAMMER TACKER A54




troonomic Handle Gr

A54

A54 (140 Type) Hammer Tacker (140/6-12mm)

Professional		Code:	1173	
140 Staples 6-12mm (Capacity 175)	0.9kg			rade = 6 Units ransit = 18 Units

Ideal for securing roofing felt with 140/12mm stainless steel staples. The surface protection plate also enables this tool to rapidly secure sheeting and breather membrane without tearing it.



Great value bundles

Tough all-metal hammer tackers designed to offer the best in speed and performance for many high volume fixing tasks. Supplied with a choice of Tacwise fastenings in various leg lengths and pack sizes. Suitable for a range of fixing jobs including securing flooring underlay, roofing felt, sheeting, breather membrane and many more.

A54 (140 Type) Hammer Tacker Bundle 140/6-12mm



The surface protection plate enables this tool to rapidly secure sheeting and breather membrane without tearing it. Supplied with 5000 stainless steel staples.

A11 (140 Type) Hammer Tacker Bundle 140/6-10mm





Staple Remover

Ideal for wood

The Tacwise staple remover is ideal for lifting out a variety of staples from timber. It grips and retains staples whilst removing them. The ergonomic handle grip provides comfort during extended periods of use. Designed to safely and securely remove fastenings from a range of materials, our staple remover is the ideal addition to every tool kit.



The Pro Staple Remover grips and retains staples whilst removing them. Perfect for lifting out many types of staples from panelling, insulation & lining, upholstery, carpet underlay and many more. Plus with built-in Germ-Savvy[®] antibacterial protection in the handle; tested to – ISO 22196:2011.



Many Tools For Each Staple Family

Features			Air vents	All metal construction	Belt hook	Bottom loading magazine	Extended cutaway nose	Removable battery 12V	Full length cable guide	Impact power adjuster	Impact resistant metal body	LED work light	Lock-down handle	Long power cord	On/off switch	Personalisation window	Recessed cutaway nose	Removable margin edge adjuster	Safety contact nose	Staple/nail viewing window	Takes 53 & 13 staples	Tough polymer lightweight body	Trigger lock mechanism	USB rechargeable battery 4V	Wide ergonomic grip
13 Series	Code	Description																							
Z2 53-13M	1218	Compact, metal and tough		٠	•	٠					•		•			٠		•		٠	•				
Z2 53-13L	1727	Durable, compact and lightweight			•	٠							٠			•				•	•	•			
Z2 53-13T	1728	Stylish, compact and lightweight			•	٠							٠			٠				٠	•	•			
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types		٠	•	•				٠	•		٠			٠	•	•		•	•			1	Ð
A19 – Hammer	1327	Takes 53 and 13 type staples		•																	•			1	
Hobby 53-13EL - 4V	1563/1564	Rechargeable via USB	•		•	•						•			•				•		•			•	•
53-13EL – 12V	1565/1632	Removable, rechargeable battery	•		•	•		•				•			•				•		•			1	•
Hobby 53 & 13EL	1702	Compact corded electric	•			•						•		•	•				•	•	•	•	•	1	•
140 Series																									
Z4-140 (4-in-1)	1747	Professional, firing 4 fastening types		٠	•	•				٠	•		٠			•	•	•		•				1	Ð
A11 – Hammer	0322	Traditional hammer tacker		•																				1	Ð
A54 – Hammer	1173	Heavyweight hammer tacker		•																				•	•
140-180EL - 12V	1586/1603	Removable, rechargeable battery	•		•	•		•				•			•				•						•
140EL Pro	1703	Compact corded electric	•			•						•		•	•				•	•		•	•	,	•
A14014V - Air	A14014V	Compact air powered				٠																	•	,	•
53 Series																									
Z2 53-13M	1218	Compact, metal and tough		٠	•	٠					•		٠			٠		•		•	•				
Z2 53-13L	1727	Durable, compact and lightweight			•	٠							•			•				•	•	•			
Z2 53-13T	1728	Stylish, compact and lightweight			•	•							•			•				•	•	•			
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types		•	•	•				•	•		•			•	•	•		•	•				
A19 – Hammer	1327	Taking both 53 and 13 type staples		•																	•			,	•
Hobby 53-13EL - 4V	1563/1564	Rechargeable via USB	٠		•	•						•			•				•		•			•	•
53-13EL – 12V	1565/1632	Removable, rechargeable battery	•		•	•		•				•			•				•		•			,	•
Hobby 53 & 13EL	1702	Compact corded electric	•			•						•		•	•				•	•	•	•	•		•
Cable Tacker																									
Z-CT Duo	1749	Professional, takes CT-45 & CT-60 staples		•	•	•	•		•	•	•		•			•				•					•
71 Series						_										_		_		_		_		_	
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types		٠	٠	٠				٠	•		٠			٠	•	•		•	•				•
91 Series																									
Z4-140 (4-in-1)	1747	Professional, firing 4 fastening types		٠	٠	•				•	•		•			•	•	•		•					•



Application	IS	Alarm/data cable	Blinds & awnings	Building membranes	Carpeting & underlay	Damp proof coursing	Display/shop fitting	Exhibition/shows	Fabrics & blinds	Heavy textiles (leather, canvas)	Hobby crafts	Insulation (Roll)	Light carpentry	Masonite	Moulding & beading	Netting/wire fencing	Picture framing	Posters/displays	Plastic sheeting	Roofing	Schools/education	Tarpaulin	Telecommunications	Theatre/film scenery	Thinner boards	Trellis/garden	Underfloor heating	Upholstery	Weather strips	Window dressing
13 Series	Code																													
Z2 53-13M	1218						•	٠	•		•	٠				٠	•	•			•			•		٠		•		
Z2 53-13L	1727								•		•						•	٠			•			٠		٠				
Z2 53-13T	1728								•		•						•	•			•			•		٠				
Z5-53 (5-in-1)	1748						•	•	•	•	•		•		•	•	•	•			•			•	•	•		•	•	•
A19 – Hammer	1327		٠				•	•	•		•	•						•	•		•			•						•
Hobby 53-13EL - 4V	1563/1564		٠				•	•	•		•	•	•		•		•	•			•			•	•			•	•	•
53-13EL – 12V	1565/1632		•				•	•	•		•	•	•		•		•	•						•	٠			•	٠	•
Hobby 53 & 13EL	1702		٠				•	•	•	•	•	•	•				•	•						•	•			•	•	•
140 Series																														
Z4-140 (4-in-1)	1747		٠	٠	٠	٠	•	٠	•			٠		٠	•	٠	•		•	٠		٠		٠	•	٠	•	•		•
A11 – Hammer	0322				٠			•				٠				•			•											
A54 – Hammer	1173				٠														•	•										
140-180EL - 12V	1586/1603		٠	٠	٠	•	•	•	•			•		•	•	٠	•	•	•	•		•			٠	•	•	•		
140EL Pro	1703		٠	•	٠	•	•	•	•			•		•	•	•	•		•	•		•					٠			
A14014V – Air	A14014V		•	•	•	•	•	•	•			•		•		•	•		•			•					٠			
53 Series																														
Z2 53-13M	1218						•	•	•		•	٠				٠	•	•			•			٠		٠		٠		
Z2 53-13L	1727								•		•						•	•			•			٠		٠				
Z2 53-13T	1728								•		•						•	•			•			•		٠				
Z5-53 (5-in-1)	1748						•	•	•	•	•		•		•	•	•	•			•			•	•	•		•	•	•
A19 – Hammer	1327		٠				•	٠	•		•	•						•	•		•			•						•
Hobby 53-13EL - 4V	1563/1564		•				•	•	•	•	•	•	•		•		•	•			•			•	•			•	•	•
53-13EL – 12V	1565/1632		٠				•	•	•	•	•	•	•		•		•	•						٠	•			•	•	•
Hobby 53 & 13EL	1702		٠				•	•	•	•	•	•	•				•	•						•	٠			•	•	•
Cable Tacker																														
Z-CT Duo	1749	•														•							•							
71 Series			_		_																			_			_		_	
Z5-53 (5-in-1)	1748						•	•	•	•	٠		•		•	•	•	•			•			•	•	٠		•	٠	•
91 Series	1747																													
Z4-140 (4-in-1)	1747		•	•	•	•	•	•	•			•		•	•	•	•		•	•		•		•	•	•	•	•		•

Specificatio	ons		Approx. Char	ge Time/Shots	Dimensions in mm
10.0	0.4	Description (Occasion	ç	e (4 & 12V)	(H x W x D)
13 Series Z2 53-13M	Code 1218	Description/Overview	Time (hr)	Shots	85 x 165 x 39
		Compact, metal and tough	_	_	
Z2 53-13L	1727	Durable, compact and lightweight	-	-	85 x 165 x 39
Z2 53-13T	1728	Stylish, compact and lightweight	-	-	85 x 165 x 39
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types	-	-	120 x 192 x 35
A19 – Hammer	1327	Takes 53 and 13 type staples	-	-	45 x 278 x 32
Hobby 53-13EL – 4V	1563/1564	Rechargeable via USB	1.5	850 - 1000	147 x 47 x 150
53-13EL – 12V	1565/1632	Removable, rechargeable battery	3 – 5	3000 - 4000	150 x 50 x 180
Hobby 53 & 13EL	1702	Compact corded electric	-	-	161 x 188 x 54
140 Series					
Z4-140 (4-in-1)	1747	Professional, firing 4 fastening types	-	-	120 x 192 x 35
A11 – Hammer	0322	Traditional hammer tacker	-	-	65 x 305 x 43
A54 – Hammer	1173	Heavyweight hammer tacker	-	-	78 x 308 x 35
140-180EL - 12V	1586/1603	Removable, rechargeable battery	3 – 5	3000 - 4000	150 x 50 x 180
140EL Pro	1703	Compact corded electric	-	-	160 x 188 x 54
A14014V - Air	A14014V	Compact air powered	-	-	235 x 46 x 159
53 Series					
Z2 53-13M	1218	Compact, metal and tough	-	-	85 x 165 x 39
Z2 53-13L	1727	Durable, compact and lightweight	-	-	85 x 165 x 39
Z2 53-13T	1728	Stylish, compact and lightweight	-	-	85 x 165 x 39
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types	-	-	120 x 192 x 35
A19 – Hammer	1327	Taking both 53 and 13 type staples	-	-	45 x 278 x 32
Hobby 53-13EL - 4V	1563/1564	Rechargeable via USB	1.5	850 - 1000	147 x 47 x 150
53-13EL – 12V	1565/1632	Removable, rechargeable battery	3 – 5	3000 - 4000	150 x 50 x 180
Hobby 53 & 13EL	1702	Compact corded electric	-	-	161 x 188 x 54
Cable Tacker					
Z-CT Duo	1749	Professional, takes CT-45 & CT-60 staples	-	_	124 x 190 x 35
71 Series					
Z5-53 (5-in-1)	1748	Professional, firing 5 fastening types	-	_	120 x 192 x 35
91 Series					
Z4-140 (4-in-1)	1747	Professional, firing 4 fastening types	-	-	120 x 192 x 35



Weight (kg)	Magazir	e Capacity	Fa: Type	Minimum Firing Distance From Wall	
	Nails	Staples	Nails	Staples	
0.3	-	105(53) 110(13)	-	53/4-8mm & 13/4-8mm	8mm
0.2	-	105(53) 110(13)	-	53/4-8mm & 13/4-8mm	9mm
0.2	-	105(53) 110(13)	190/190\/10 15mm 8 52/6 14mm 12/6 14mm		9mm
0.6	90	150(53) 156(13) 145(71)			8mm
0.4	-	120	_	53/6-10mm & 13/6-10mm	-
0.6	50	100	180/10mm	53/6-12mm & 13/6-12mm	15mm
0.9	85	140	180/10mm	53/6-12mm & 13/6-12mm	15mm
0.8	85	145(53) 150(13)	180(18G)/10-14mm	53/8-14mm & 13/8-14mm	15mm
0.6	90	83(140) 100(91)	180(18G)/10-15mm & 180 Headless/15mm	140/6-14mm & 91/6-14mm	7mm
0.9	-	150	-	140/6-10mm	-
0.9	-	175	-	140/6-12mm	-
0.9	85	84	180/10mm	140/6-12mm	15mm
0.8	85	85	180(18G)/10-14mm	140/8-14mm	15mm
0.9	-	150	-	140/4-14mm	16mm
0.3	-	105(53) 110(13)	-	53/4-8mm & 13/4-8mm	8mm
0.2	-	105(53) 110(13)	-	53/4-8mm & 13/4-8mm	9mm
0.2	-	105(53) 110(13)			9mm
0.6	90	150(53) 156(13) 145(71)	180(18G)/10-15mm & 180 Headless/15mm	53/6-14mm, 13/6-14mm & 71/6-14mm	8mm
0.4	-	120	-	53/6-10mm & 13/6-10mm	-
0.6	50	100	180/10mm	53/6-12mm & 13/6-12mm	15mm
0.9	85	140	180/10mm	53/6-12mm & 13/6-12mm	15mm
0.8	85	145(53) 150(13)	180(18G)/10-14mm	53/8-14mm & 13/8-14mm	15mm
				OT 15/0 10mm	
0.6	-	85	_	CT-45/8-10mm & CT-60/10-14mm	7mm
0.6	90	150(53) 156(13) 145(71)	180(18G)/10-15mm & 180 Headless/15mm	53/6-14mm, 13/6-14mm & 71/6-14mm	8mm
0.6	90	83(140) 100(91)	180(18G)/10-15mm & 180 Headless/15mm	140/6-14mm & 91/6-14mm	7mm

Colour coded

Useful and convenient for quickly selecting the correct fastenings for Tacwise and other popular tools.



Cordless Nailing & Stapling

Rang

Stapling up to 12mm / Nailing up to 10mm

Cordless 4V

Lightweight & Convenient

Versatile and lightweight staple & nail guns providing accurate results; the tools in the Tacwise 4V cordless range are rechargeable via USB for convenience. Suitable for a wide range of DIY, hobby and more ambitious tasks at home, in the garden and at school.



Hobby 53-13EL

Suitable for a variety of DIY and hobby projects, the Cordless 4V Hobby 53-13EL is a lightweight and convenient staple and nail gun. With a storage bag, handy belt hook, safety contact tip, a viewing window for fastenings, an LED light and a safety on/off switch for effortless use and safety.



With an on/off LED light for precision and ease-of-use and a bottom loading magazine for switching between staples and nails without any adjustment, these 4V staple/nail guns also feature a safety contact nose, belt hook and staple/nail viewing window. The Hobby 53-13EL comes backed by a 2-year guarantee, but remember to use genuine Tacwise staples and nails as dimensions, tolerances and hardness from other sources are not always to the same Tacwise's exacting standards.

Storage Bag

Made from the same high quality material as marine dive suits, offering great protection for tools and accessories.

(TACWISE)

Cordless 12V

For hours of continuous stapling/nailing

Powered by an interchangeable 12V lithium-ion battery, our durable cordless range is ideal for busy trades and enthusiastic DIYers. Both tools in the range include great features such as a work light, safety contact nose and belt hook, as standard. Offering greater power, battery life and user comforts.



140-180EL Cordless 12V Staple/Nail Gun

140/6 12mm 190/190\/10

140/0-12									
Semi-Professional		Code: 1586	Includes: Battery, UK mains charger, Euro plug adaptor, 200pcs 140 staples, 200pcs 180 nails, storage bag						
		Code: 1603	Includes: Tool body only						
(Capa ∏ 180 (Staples 6-12mm Icity 84) 18G) Nails 10mm Icity 85)	0.8kg (Tool Only)	LED Work Light	Storage Bag	UK Charger	Euro Adaptor	Hanging Retail Box	Trade = 1 Units Transit = 10 Units	

A powerful staple/nail gun firing the heavier 140 gauge staple, preferred by professionals. Which provides excellent holding power on materials such as plastic sheeting and netting. This compact tool delivers consistent results time after time.



BeltHanger

12V Li-ion Battery

The fast-charging, interchangeable quick release battery for Tacwise 12V tools.

Code: 1582 - Battery only





53-13EL Cordless 12V Staple/Nail Gun

E0/0 10mm 10/0

	53/0-1211111 13/0-		(186)/1011111							
	Semi-Professional	Code: 1565		Includes: Battery, UK mains charger, Euro plug adaptor, 200pcs 53 staples, 200pcs 13 staples, storage bag						C
(53 Staples 6-12mm (Capacity 140) 13 Staples 6-12mm (Capacity 140)	180(18G) Na (Capacity 85		LED Work Light	Storage Bag	UK Charger	Euro Adaptor	Hanging Retail Box	Trade = 1 Units Transit = 10 Units	

This model offers all the benefits of the 140-180EL tool but fires both 53 and 13 fine wire staples, and a 10mm nail, without any need for adjustment. These finer staples are ideal where a neat/discrete finish is required.

TACMISE)

Cordless Nailing & Stapling Stapling up to 25mm / Nailing up to 32mm

Cordless 12V 32mm ^(IV) for Spring 2024

Speed, precision and versatility

(Capacity 100)

Work Light

Charger

Adaptor

Box

Transit = 4 Units

Capable of firing 180 (18G) nails up to 32mm and 91 staples up to 25mm, the Master Nailer™ 12V 191 is ideal for second fix tasks and precision work. Featuring an efficient single shot trigger, LED work light, safety on/off switch and built-in depth adjuster, the Master Nailer[™] 12V 191 offers ease of use, affordability and excellent performance.











12V Li-ion Battery

Using the most recent lithium-ion technology for the best weight and power delivery.

The mains-supplied DC charger, which works with both UK and Euro plugs, connects directly into the battery, eliminating the need for a charging dock. The battery features an LED charging cycle indicator – red when charging and green when the charge cycle has finished.

Code: 1582 – Battery only





Thenes

Cordless 20V 32mm for Spring 2024

Speed, precision and versatility with impressive battery life between charges

Our 20V Cordless Master Nailer[™] 191 hosts all the benefits of the 12V Cordless 191 tool but with an extended battery life delivering around 1000 shots between charges. Designed for the Tacwise 20V Safety Battery, the Master Nailer[™] 20V 191 offers professionals endurance and optimum performance.

Master Nailer[™] 20V 191 Cordless Staple/Nail Gun 91/15-25mm 180(18G)/15-32mm

Includes: 12V battery UK mains fast charger, Euro plug Code: 1701 Semi-Professional adaptor, 1000pcs 91 staples, 2000pcs 180 nails 91 Staples 15-25mm (Capacity 100) $\langle \hat{} \rangle$ 180 (18G) Nails 15-3 (Capacity 100) 2 4kr LED




Belt Hange

TACWISE

Our lithium-ion battery is designed especially for Tacwise 20V tools and features a unique on/off switch on the battery itself for an added layer of safety. The compact DC mains charger connects directly into the battery, eradicating the need for large charging docks and has a quick 1-hour fast charge time.

Both lightweight and compact, the battery is easy to load and features an LED charging status indicator.





Built-in Depth Adjust

10ad Pro Metal Magazin

TACIVIISE

Cordless Nailing & Stapling Stapling up to 40mm / Nailing up to 50mm

Cordless 18V

Perfect for a variety of second fix tacks

Built-in Depth Adjus

This 18V model boasts a host of user benefits including a fast charge system Ranger EL-PRO carries a powerful slide-on 18V battery system.





Inc

'n





Versatile

Extremely versatile, firing staples up to 40mm and nails up to 50mm, the Ranger EL-PRO is a heavyweight cordless option. Not to be confused with others on the market, this Tacwise tool enjoys all of the engineering capabilities and know-how built from 60+ years of experience.

Ranger EL-PRO 18V Cordless 2-in-1 Staple/Nail Gun (91/19-40mm) (180(18G)/20-50mm)

Pr	rofessional	Code: 1506		Includes: 18V battery, UK mains charger, Euro plug adaptor, hex wrench, 1000pcs 91 staples, 1000pcs 18G nails							
י י ר ר	91 Staples 19-40mm (Capacity 100) 180 (18G) Nails 20-50 (Capacity 100)	<u> </u>	LED Work Light	UK Charger	Euro Adaptor	Carry Case	Trade = 1 Unit				

When firing this tool, even with the longest fastenings, its recoilless action is immediately obvious. Which takes the stress out of simple fixing tasks and becomes a real win, when in continuous use. Heavyweight, well balanced and loaded with great user features as standard... The hallmark of the Tacwise brand.

Carry Case

The Ranger EL-PRO carry case has been designed to be oversized to conveniently store multiple packs of staples and nails.





Comes with a UK/Euro cable/adaptor.





Compact Electric Tackers

Fast, reliable & loaded with features

The new generation of compact electric stapler & nailers, supplied with 5000 staples and 2000 nails. Staple and nail function in one tool with a bottom loading magazine for easy access and simple switching between staples and nails of various leg lengths without any adjustment. Also featuring an LED work light and a long 2m power cord for ease of use.

Designed with safety in mind, these tools have an on/off power switch, trigger lock mechanism and safety contact nose, all of which must be activated for the tool to fire. Both these tools come with an interchangeable plug for UK and Euro power outlets, fitted ready for UK use.

Semi-Professional	Code: 1703	Includes: 5	5000pcs 14	40 staples	s & 2000p	cs 180 (18G) n	nails	=	
140 Staples 8-14mn (Capacity 85)	n 🔺	Щ (7 7]			-	🗑 💵	
(Capacity 85) 180 (18G) Nails 10-1 (Capacity 85)	4mm 0.84kg	Euro Pla Adaptor Bo		e = 1 Unit sit = 10 Units	S		1	TAGWISE	
obby 53 & 13	3EL 53/8-1	4mm 13/	/ <mark>8-14mm</mark>	180(18	8G)/10-14n	IM NEW			
Obby 53 & 13	3EL 53/8-1 Code: 1702				,	111 NEW 25 180 (18G) na	nails		







UK's favourite corded nail gun


Suitable for a wide range of second fix and fastening tasks, these electric nailers and staplers achieve great results with minimal effort.

The dedicated nailing version of our top-selling 191EL Pro, the 181ELS is a versatile tool that fires 180 (18G) nails up to 35mm. Feature-rich, the 181ELS is highly practical and lightweight, perfect for repetitive nailing tasks.

Master Nailer[™] 181ELS Pro Electric Nailer 180(18G)/15-35mm



Extraordinary value for money and a must for every tool bag. Coupling superb performance with user comfort, our Medium Duty electric tackers are extremely fast semi-professional tools capable of firing nails up to 35mm.





191EL Pro

Stapling & nailing

Firing six different lengths of nails and four different lengths of staples. The 191EL Pro is a nailer and stapler that's perfect for a wide range of fixing applications. Versatile, ergonomic and lightweight; the 191EL Pro is perfect for continuous fastening tasks – especially those in difficult to reach areas. Simple, easy to use and the fastest tool of its kind. It's no wonder the 191EL Pro is the UK's favourite nailer/stapler.

Ultimate Versatility

191EL Pro is a 'must have' for all professional trades tackling any number of second fix tasks as well as precision jobs in the workshop. Hugely popular for flooring including boarding out and soft wood floorboards.





Duo 35

Stapling/nailing & loaded with features

A compact tool with tremendous versatility, the Duo 35 combines unrivalled performance with speed and precision. With all-new electronics, enhanced switch-gear and improvements throughout, this nailer and stapler is another great addition to the exciting generation of electric tools from Tacwise.





Master Nailer[™] Duo 35 Electric Nailer/Stapler 91/15-30mm 180(18G)/15-35mm

	Drefessional		Code: 11	65	
	Professional	Coc	le: 1167 (EURO)	
	91 Staples 15-30mm (Capacity 100)				ſ
	180 (18G) Nails 15-3 (Capacity 100)	5mm	1.8kg	Carry Case	Trade = 1 Unit Transit = 4 Units



The Duo 35 is fully loaded with a host of innovative features which include; a flip open nose gate, an all metal professional magazine, a nose safety device, power light and a separate on/off switch.

Duo 35 Tool Versatility

Perfect for precision as well as demanding fixing jobs. The Duo 35 has been re-designed with the trades in mind, so you can work on flooring, panelling or skirting, architrave and more. The Duo 35 is an essential tool for second fix jobs, compact, durable and affordable.







TACWISE

18G/50 Nailer

Pro 18G brad nailer

This dedicated nailing tool has a precision air tool construction that will accurately drive 18 gauge brads with little marking to the surface of the timber. Ideal to speed through a wide variety of tasks saving a lot of time and freeing one hand to guide and position the work piece. Also ideal for a temporary fix during glue drying.



Master Nailer[™] 18G/50 Electric Nailer 180(18G)/20-50mm

Code: 1707 Includes: 1000pcs 180 nails

180 (186) Nails 20-50mm (Capacity 100)

Professional



-

Feature rich, this powerful electric nailer boasts a flip open nose gate, a high capacity magazine as well as a useful belt hook. The 18G/50 is capable of firing 18 gauge (type 180) nails from 20 to 50mm in length and delivers precise results on applications including: soft and medium woodwork, flooring and panelling. Features our fast loading system and does not require gas packs or compressors.

All New Magazine

2.3kg

The 18G/50 Nailer has a new style magazine for highly accurate fastening and features two nail viewing windows for user convenience. The rapid release nose gate and simple side loading mechanism are features shared by the new generation of medium and heavy duty Tacwise electrics.





Heavy Duty Corded Electrics

1

Removeable Wire Stan

400ELS Pro Inclined Nailer

Angled for easy access

NIe Quick R



	Code: 07		No nails included]
Professional	Code: 0876 (. ,		
	Code: 17	/04	Includes: 1000pcs 500 nails	NEW
500 (18G) Angled Nails 15-40 (Capacity 100)	mm 1.8kg	Carry Case	Trade = 1 Unit Transit = 4 Units	

Fast and light, this handy angled nailer makes it ideal for tackling fixing tasks where elbow room or access is limited – such as under stairs, behind baths or sanitary ware. Delivering the closest thing to air tool performance in an electric nailer, it fires six lengths of nail up to 40mm, and at speeds of up to 30 nails per minute.



• Whilst stocks last









, old




An Unrivalled Performance

400ELS is a little different from the other Tacwise electrics. The key feature is its angled magazine which makes the tool extremely compact and capable of firing into very tight spaces. It also features a unique, removeable wire stand, which means that the tool is in the upright position 'ready to go' when used in tasks such as securing floor boards and boarding out.

Tough Storage/Carry Case

All our heavy-duty electric tools come supplied in a sturdy carry case.





At a Glance Cordless & Corded Electrics

Features			Air vents	Belt hook	Bottom loading magazine	Depth control	Impact resistant body	LED work light	Long power cord	Metal magazine	Nose protector	Personalisation window	Quick release loading	Quick release nose gate	Rechargeable li-ion battery	Safety contact nose	Safety on/off light	Safety on/off switch	Single shot trigger	Staple/nail viewing window	Trigger safety lock switch	Wide ergonomic grip
Cordless	Code	Description																				
Hobby 53-13EL - 4V	1564	Compact, great value cordless	٠	٠	•		•	٠		•					•	•		٠	•	•		•
53-13EL – 12V	1565/1632	Extensive shots per battery charge	•	٠	•		•	٠		•					•	•		٠	•	•		•
140-180EL - 12V	1586/1603	Extensive shots per battery charge	•	٠	•		•	٠		•					•	•		٠	•	•		•
12V 191	1700	Versatile/affordable cordless up to 32mm	•	٠		٠	•	٠		•			•		•	•		٠	•	•		•
20V 191	1701	Versatile/pro cordless up to 32mm	•	•		٠	•	٠		•			•		•	•		٠	•	•		•
Ranger EL-PRO – 18V	1506	Powerful and extremely versatile tool	•	•		•	•	٠		•	•		•		•	•			•	•		•
Compact Corded																						
Hobby 53 & 13EL	1702	Compact feature rich corded electric	٠		•		•	٠	•	•						•		٠	•	•	•	•
140EL PRO	1703	Compact feature rich corded electric	•		•		•	٠	•	•						•		•	•	•	•	•
Medium Duty Cor	ded																					
181ELS	1176/1705/1718	Best selling electric brad nailer	•				٠			٠	•		•	٠		٠		٠	•	•		•
191EL Pro	0327	Versatile electric brad nail/staple gun	٠				•			•	٠		٠			•		٠	•	•		•
Heavy Duty Corde	d																					
Duo 35	1165/1167	Versatile, corded for staples and nails	٠				٠		•	٠	•		•	٠		•	•	٠	•	•		•
18G/50	1707	Dedicated corded brad nailer	•	٠			•		•	•	•	•	•	•		•	•	٠	•	•		•
400ELS Pro	0733/0876/1704	Professional angled nailer	•				•		•	•	•		•	•		•		•	•	•		•

Specifications	5	Dimensions in mm (H x W x D)	Weight (kg)	Magazir	ne Capacity	Fastener T	ype/Length	Min. firing distance from wall
Cordless	Code			Nails	Staples	Nails	Staples	
Hobby 53-13EL - 4V	1564	147 x 47 x 150	0.6	50	100	180(18G)/10mm	53/6-12mm & 13/6-12mm	15mm
53-13EL – 12V	1565/1632	150 x 50 x 180	0.9	85	140	180(18G)/10mm	53/6-12mm & 13/6-12mm	15mm
140-180EL - 12V	1586/1603	150 x 50 x 180	0.9	85	84	180(18G)/10mm	140/6-12mm	15mm
12V 191	1700	264 x 65 x 234	2.2	100	100	180(18G)/15-32mm	91/15-25mm	23mm
20V 191	1701	264 x 65 x 240	2.4	100	100	180(18G)/15-32mm	91/15-25mm	23mm
Ranger EL-PRO – 18V	1506	267 x 85 x 295	3.0	100	100	180(18G)/12-50mm	91/19-40mm	20mm
Compact Corded								
Hobby 53 & 13EL	1702	160 x 188 x 54	0.8	85	145 (53) & 150 (13)	180(18G) 10-14mm	53/8-14mm & 13/8-14mm	15mm
140EL Pro	1703	160 x 188 x 54	0.8	85	85	180(18G) 10-14mm	140/8-14mm	15mm
Medium Duty Corded								
181ELS Pro	1176/1705/1718	230 x 255 x 68	1.6	100	-	180(18G) 15-35mm	-	25mm
191EL Pro	0327	230 x 255 x 68	1.8	100	100	180(18G) 15-35mm	91/15-30mm	25mm
Heavy Duty Corded								
Duo 35	1165/1167	235 x 271 x 66	1.8	100	100	180(18G) 15-35mm	91/15-30mm	25mm
18G/50 Brad Nailer	1707	296 x 277 x 80	2.3	100	-	180(18G) 20-50mm	_	25mm
400ELS Inclined Nailer	0733/0876/1704	210 x 290 x 57	1.8	100	-	500(18G Angled) 15-40mm	_	15mm
Spare nose pieces								
181ELS Spare rubber nose (5pk)	1172 (Black)	-	-	-	-	-	-	-
191EL Spare rubber nose (5pk)	0849 (Orange)	-	-	-	-	-	-	-
Duo 50 Spare rubber nose (5pk)	1206 (Black)	-	-	-	-	-	_	-

Applications	Hobby 53-13EL	53-13EL	140-180EL	12V 191	20V 191	Ranger EL-PRO	Hobby 53 & 13EL	140EL PR0	181ELS	191EL Pro	Duo 35	18G/50	400ELS Pro
Blinds & awnings	•	٠	٠				٠	٠					
Building membranes			•					٠			•		
Cabinet woodwork assembly				•	•	•			•	•	•	•	•
Cabins, mobile homes, caravans				•	٠				•	•	٠		•
Cane/rattan furniture				•	•				•	•	٠		•
Carpeting & underlay			•					•					
Damp proof coursing			•					•					
Display/shop fitting	•	•	•	•	•	٠	•	٠	٠	•	٠	•	•
Door frames & skirting				•	•	•			•	•	٠	•	•
Drawer bottoms				•	•				•	•	•	•	•
Exhibition/shows	•	•	•	•	•	•	•	•	•	•	•	•	•
External pelmets				•	•				•	•	•	•	•
Fabrics & blinds	•	•	•				•	•					
Fencing				•	•				•	•	•	•	
Garden furniture											•	•	•
Gripper & thresholds				•	•	•			•	•	•	•	
Heavier textiles inc. leather & canvas							•						
Hobby crafts	•	•					•						
Insulation (roll)	•	•	•				•	•			•	•	•
Light carpentry	•	•					•						
Masonite			•					•					
Moulding & beading		•	•	•	•	•		•	•	•	•	•	•
Netting/wire fencing	-	-	•	•	•	-		•	-		•	-	
Panelling			-	-	-	•		-		-	-		
Pet cages, runs & enclosures					•	-			•		•		-
Picture/mirror framing		•	•	•	•		•	•	•		•		
Plasterboard	•	•	•	•	•		-	•	•	•	•	•	-
Plastic sheeting			•	•	•			•		•	•		•
Roofing			•	•	•			•		•	•	•	-
			•	•	•			•	•	•	•		•
Saunas				•	•				•	•	•		
Sheds & garden buildings Shoe repair				•	•				•	•	•		
Soft medium wood flooring				•	•				•	•	•		-
				•	•				•	•	•	•	•
Staircase/bannister construction				•	•	•			•	•	•		•
Subflooring/boarding out				•	•				•	•	•		•
Tacking plasterboard/pre-screwing				•	•				•	•	•	•	•
Tacking with glue applications			-	•	•				•	•	•		•
Tarpaulin			•					•					
Theatre/film scenery	•	•		•	•		•		•	•	•	•	•
Thinner boards	•	•	•				•						
Tongue & groove flooring				•	•	٠			•				•
Trellis/panelling			•	•	•				•	•	•	•	•
Underfloor heating			•					•					
Upholstery	•	•	•				•						
Weather strips	•	•					•						
Window dressing	•	•		٠	•		•			٠	•	•	•
Window frames & beading						•							

TACWISE

Staple families at a glance





		CT-45 CT-60	91 Series	71 Series
Hand	Heavy Duty (6-14mm)		Z4-140 4-in-1 (1747, 1764)	Z5-53 5-in-1 (1748, 1765)
	Cable	Z-CT Duo (1749, 1763)		
	12V		12V 191 (1700)	
Cordless	20V		20V 191 (1701)	
	18V		Ranger EL-PRO (1506)	
Electric	Corded Medium Duty		191EL Pro (0327)	
Elec	Corded Heavy Duty		Duo 35 (1165) Duo 35 (1167 EURO)	
Pneumatic	Air			71 Upholstery (A7116V/1190)Premium 71 (A7116P)71 Extra Long Nose (A7116LN)

Staples Hand, corded & cordless tackers

Produced from high grade raw materials, our staples are available in a range of finishes and sizes with full coverage of those most commonly used in upholstery, installation and second fix trades. Whatever the stapling task, you'll find a fastening that exceeds expectations.

Colour coded

Useful and convenient for quickly selecting the correct fastenings for Tacwise and other popular tools.



140 staples

	140 stap	ies		
_	Code	Staple Length/Type	Box Qty	For Use In
NEW	1627	140/18G Selection Pack	7700	Z3-140, Z3-140L, 140-180EL, Z4-140 (4-in-1)
NEW	1341	140 Selection Pack	4400	Z3-140, Z3-140L, Z4-140 (4-in-1), 140EL, A14014V
	0350	140 Selection Pack	4400	Z3-140, Z3-140L, Z4-140 (4-in-1), 140EL, A14014V
	0340	140/6mm	5000	Z1-140, Z1-140L, Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, A14014V
	0341	140/8mm	5000	Z1-140, Z1-140L, Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, 140EL Pro, A14014V
	0342	140/10mm 140/10mm s/steel	5000	- Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, 140EL Pro, A14014V
	0477	140/12mm	5000	
(actual size)	0343	140/12mm	5000	Z3-140, Z3-140L, Z4-140 (4-in-1), A54, 140EL, 140-180EL, 140EL Pro, A14014V
10.60mm ►	0344		5000	Z3-140, Z3-140L, Z4-140 (4-in-1), 140EL, 140EL Pro, A14014V
▲ 6mm	0345	140/6mm	2000	Z1-140, Z1-140L, Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, A14014V
	0346	140/8mm	2000	Z1-140, Z1-140L, Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, 140EL Pro, A14014V
	1216	140/8mm s/steel	2000	
V14mm V V	0347	140/10mm	2000	Z3-140, Z3-140L, Z4-140 (4-in-1), A11, A54, 140EL, 140-180EL, 140EL Pro, A14014V
	1217	140/10mm s/steel	2000	
	0348	140/12mm	2000	- Z3-140, Z3-140L, Z4-140 (4-in-1), A54, 140EL, 140-180EL, 140EL Pro, A14014V
	1220	140/12mm s/steel	2000	
	0349	140/14mm	2000	Z3-140, Z3-140L, Z4-140 (4-in-1), 140EL, 140EL Pro, A14014V
	53 staple	es		
NEW	1628	53/18G Selection Pack	10,200	Z3-53, Z5-53 (5-in-1), Hobby 53-13EL, 53-13EL
	1095	53 Selection Pack	6000	Z3-53, Z3-53L, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL
	0331	53/6mm	5000	Z2 Series, Z3-53, Z3-53L, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL
	0332	53/8mm	5000	Z1-53, Z1-53L, Z1-53T, Z2 Series, Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	0431	53/10mm	5000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	0450	53/12mm	5000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	0452	53/14mm	5000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), Hobby 53EL, Hobby 53 & 13EL
	0333	53/4mm	2000	Z1-53, Z1-53L, Z1-53T, Z2 Series
(actual size)	0334	53/6mm	2000	Z1-53, Z1-53L, Z1-53T, Z2 Series, Z3-53, Z3-53L, Z5-53 (5-in-1), A19, Hobby 53EL,
11.35mm	1268	53/6mm s/steel	2000	Hobby 53-13EL, 53-13EL
▲ 4mm	0335	53/8mm	2000	Z1-53, Z1-53L, Z1-53T, Z2 Series, Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
▼14mm	1269	53/8mm s/steel	2000	Z1-53, Z1-53L, Z1-53T, Z2 Series, Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, Hobby 53 & 13EL, 53-13EL
	0336	53/10mm	2000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL,
	1270	53/10mm s/steel	2000	Hobby 53 & 13EL
	0337	53/12mm	2000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	0338	53/14mm	2000	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), Hobby 53EL, Hobby 53 & 13EL
	53 staple	es – Hanging plastic disp	enser box	
	1478 🗕	53/10mm	2500	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), A19, Hobby 53EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	1479 🗕	53/12mm	2500	Z3-53, Z3-53L, Z3 4-in-1, Z5-53 (5-in-1), Hobby 53EL, 53-13EL, Hobby 53 & 13EL
				Hobby 53 & 13EL

• Whilst stocks last



	CT-45 ca	able tacker staples		
(actual size) 6.3mm	Code	Staple Length/Type	Box Qty	For Use In
▲ 8mm	0980	CT-45/8mm divergent white	5 x 1000	
	0352	CT-45/10mm divergent	5 x 1000	CT-45, Z3-CT45, Z-CT Duo, Combi
↓ ↓ 10mm ↓ ↓	0353	CT-45/10mm divergent white	5 x 1000	
	СТ-60 са	able tacker staples		
(actual size) 7.6 mm	0354	CT-60/10mm divergent	5 x 1000	
↓10mm	1094	CT-60/10mm divergent white	5 x 1000	
	0355	CT-60/12mm divergent	5 x 1000	CT-60, Z3-CT60, Z3-4 in 1, Z-CT Duo, Combi
	0356	CT-60/14mm divergent	5 x 1000	
↓ _{14mm} V V	0357	CT-60/14mm divergent white	5 x 1000	
	13 staple	es		
(actual size)	0232	13/4mm	5000	Z1-13, Z1-13L, Z2 Series
10.65mm	0233	13/6mm	5000	Z1-13, Z1-13L, Z3-13, Z3-13L, Z5-53 (5-in-1), A19, Hobby 13EL, Hobby 53-13EL, 53-13EL, Z2 Series
▲ 4mm	0234	13/8mm	5000	Z1-13, Z1-13L, Z3-13, Z3-13L, Z5-53 (5-in-1), A19, Hobby 13EL, Hobby 53-13EL, 53-13EL, Z2 Series, Hobby 53 & 13EL
↓14mm V V	0235	13/10mm	5000	Z3-13, Z3-13L, Z5-53 (5-in-1), A19, Hobby 13EL, Hobby 53-13EL, 53-13EL, Hobby 53 & 13EL
	0236	13/14mm	5000	Z3-13, Z3-13L, Z5-53 (5-in-1), Hobby 13EL, Hobby 53 & 13EL
	91 staple	es		
NEW	1616	91/18mm divergent	5000	191EL/S, Duo 35, Ranger 40 Duo, 191 12V, 191 20V
	1617	91/22mm divergent	5000	Ranger EL-PRO, 191EL/S, Duo 35, Duo 50, Ranger 40 Duo, 191 12V, 191 20V
NEW	0204	91 Selection Pack	2800	191EL/S, Duo 35, Duo 50, Ranger 40 Duo
NEW	1758	91/14mm	2000	Z4-140 (4-in-1)
(actual size)	0283	91/15mm	1000	
(actual 3126) 5,95mm	0287	91/18mm divergent	1000	191EL/S, Duo 35, Ranger 40 Duo, 191 12V, 191 20V
↓ 14mm	1069	91/18mm divergent s/steel	1000	
	0284	91/20mm	1000	
	0288	91/22mm divergent	1000	
▼ 45mm 🛛 🗍	1070	91/22mm divergent s/steel	1000	Ranger EL-PRO, 191EL/S, Duo 35, Duo 50, Ranger 40 Duo, 191 12V, 191 20V
	0285	91/25mm	1000	
	1071	91/25mm divergent s/steel	1000	
	0286	91/30mm	1000	Ranger EL-PRO, 191EL/S, Duo 35, Duo 50, Ranger 40 Duo
	0289	91/30mm divergent	1000	
	0746	91/35mm	1000	Ranger EL-PRO, Duo 50, Ranger 40 Duo
	0768	91/40mm	1000	
	1174	91/45mm	1000	Duo 50
	71 staple	es		

(actual size)	
	9mm
▲ 4mm	
▼16mm	

	0365	71/4mm	20,000	
	0366	71/5mm	20,000	71EL, 71ELS, A7116LN, A7116V, A7116P
<mark>∮9mm</mark>	0367	71/6mm	20,000	
$\overline{\qquad}$	1014	71/6mm s/steel	20,000	
	0368	71/8mm	20,000	
	1065	71/8mm black	20,000	
) V	0369	71/10mm	20,000	
	0373	71/10mm black	20,000	Z5-53 (5-in-1), 71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P
	0375	71/10mm s/steel	20,000	
	0370	71/12mm	20,000	
	0290	71/12mm black	20,000	
	0371	71/14mm	10,000	
	0374	71/14mm black	10,000	
	0372	71/16mm	10,000	71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P

Staples & Nails Hand, corded & cordless tackers

	80 staple	S		
(actual size) 12.8mm	Code	Staple Length/Type	Box Qty	For Use In
	0380	80/4mm	10,000	
↓ 4mm	0381	80/6mm	10,000	
	0382	80/8mm	10,000	
▼ 16mm	0383	80/10mm	10,000	80ELS, A8016V, A8016LN
V V	0384	80/12mm	10,000	
	0385	80/14mm	10,000	
	1141	80/16mm	10,000	
(actual size)				
11.20mm	73 staple	s		
▲ 8mm	1227	73/8mm divergent s/steel	5000	
	0456	73/10mm	5000	HD-73,
	0457	73/12mm	5000	All 31 Type Pliers
tranm V V	1389	73/12mm chisel s/steel	5000	

The largest range of quality nails in Europe, manufactured from premium grade materials to exacting standards. With an ever increasing range of stainless steel for external applications.

	180 (18G) nails										
	Code	Nail Length/Type	Box Qty	For Use In								
NEW	1628	18G/53 Selection Pack	10,200	Z3-53, Z5-53 (5-in-1), Hobby 53-13EL, 53-13EL								
NEW	1627	18G/140 Selection Pack	7700	Z3-140, 140-180EL, Z4-140 (4-in-1)								
	0205	180 Selection Pack	4000	181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo, 191 12V, 191 20V								
	0359	180/15mm	2000	Z3 Series, Z4-140 (4-in-1), Z5-53 (5-in-1), 140EL, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo, 191 12V, 191 20V								
	0360	180/20mm	1000									
	0361	180/25mm	1000									
	1066	180/25mm s/steel	1000	Ranger EL-PRO, 181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G,								
(actual size) 도구	0362	180/30mm	1000	Ranger 40 Duo, 191 12V, 191 20V								
Nail = []	1067	180/30mm s/steel	1000									
Head [⊔] ▲ 15mm	0363	180/32mm	1000									
	0364	180/35mm	1000	Ranger EL-PRO, 181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G,								
1 2	1068	180/35mm s/steel	1000	Ranger 40 Duo								
↓ ▼ 50mm	0747	180/40mm	1000	Ranger EL-PRO, 191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo								
, v	1156 • 180/50mm 1000 Ranger EL-PRO, 191EL/S, Duo 50, 18G/50, Ranger 2											
	180 nails	180 nails – Hanging plastic dispenser box										
	1509	180/15mm s/steel	2000	Z3 Series, Z4-140 (4-in-1), Z5-53 (5-in-1), 140EL, Hobby 53EL, 181ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo, 191 12V, 191 20V								
	1510	180/20mm s/steel	1000	Ranger EL-PRO, 181EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo, 191 12V, 191 20V								
	1511	180/40mm s/steel	1000	Ranger EL-PRO, 191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo								
	1512	180/50mm s/steel	1000	Ranger EL-PRO, 191EL/S, Duo 50, 18G/50, Ranger 2 18G								
NEW	18G brad		5000									
	1724	18G/14mm	5000	Z4-140 (4-in-1), Z5-53 (5-in-1), Hobby 53 & 13EL, 140EL Pro								
	1708	(18G/15mm)	4000	Z3 Series, Z4-140 (4-in-1), Z5-53 (5-in-1), 140EL, Hobby 53EL, 181 ELS, 191EL/S, Duo 35, Duo 50, Ranger 2, Ranger 40 Duo, 191 12V, 191 20V								
	1709	(18G/20mm)	4000									
	1710	(18G/25mm)	4000	Ranger EL-PRO, 181 EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G,								
	1711	18G/30mm	4000	Ranger 40 Duo, 191 12V, 191 20V								
	1712	18G/32mm	4000									
	1713	(18G/35mm)	4000	Ranger EL-PRO, 181 EL/S, 191EL/S, Duo 35, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo								
	1714	18G/40mm	4000	Ranger EL-PRO, 191EL/S, Ranger 2, Duo 50, 18G/50, Ranger 2 18G, Ranger 40 Duo								
	1715	18G/50mm	4000	Ranger EL-PRO, 191EL/S, Duo 50, 18G/50, Ranger 2 18G								



(actual size)

15mm

180 head	dless pins		
Code	Nail Length/Type	Box Qty	For Use In
0478	180/15mm	2000	Z3 Series, Z4-140 (4-in-1), Z5-53 (5-in-1)

500 angled nails (18G angled brad nails)

(actual size)	20mm
Nail = [] Head	
	26°
	50mm

(actual size)	20mm
Nail = [] Head	
	26°
	50mm

tual size)	20mm	0479
	<i>7</i> ?†	1131
il = [] ad		048
	/	048
4		048
		048
-	▼ 50mm	048
	oonini	048

0823	500/20mm	5000								
0824	500/25mm	5000	400EL, 400ELS, 500EL							
0826	500/35mm	5000	400EL, 400ELS, 500EL							
0827	500/40mm	5000								
0829 🗕	500/50mm	5000	500EL							
0479	500/20mm	1000								
1131	500/20mm s/steel	1000								
0480	500/25mm	1000	400EL, 400ELS, 500EL							
0481	500/30mm	1000								
0482	500/35mm	1000								
0483	500/40mm	1000								
0484	500/45mm	1000								
0485	500/50mm	1000	500EL							
1135	500/50mm s/steel	1000								

160 (16G) stainless steel finish nails


1096	160/32mm s/steel	1000	16G/45. Ranger 2 16G
1097	160/38mm s/steel	1000	100/45, hallyel 2 100
1098	160/50mm s/steel	1000	Ranger 2 16G

16G finish nails

		n nans		
	0665	16G/20mm	2500	
	0666	16G/25mm	2500	16G/45
	0293	16G/30mm	2500	
) 11	0294	16G/32mm	2500	
lail = 📋 📗 lead	0295	16G/35mm	2500	
	0296	16G/38mm	2500	16G/45, Ranger 2 16G
	0319	16G/40mm	2500	
	0297	16G/45mm	2500	
Ä	0298	16G/50mm	2500	
\bigvee	0299	16G/55mm	2500	Denser 0.160
	0300	16G/60mm	2500	Ranger 2 16G
	0301	16G/64mm	2500	



16G angled finish nails



se angle			
0769	16G/32mm	2500	
1222	16G/32mm s/steel	2500	
0770	16G/38mm	2500	
1223	16G/38mm s/steel	2500	
0771	16G/45mm	2500	Ranger 2 16G Inclined, DeWalt [™] DC618. DCN660.
1224	16G/45mm s/steel	2500	Paslode [®] IM250A, IM65A F
0772	16G/50mm	2500	
1225	16G/50mm s/steel	2500	
0773	16G/63mm	2500	
1226	16G/63mm s/steel	2500	

F16 Nailers

Whilst stocks last

Cordless 4V

DIY/semi-pro glue gun

Lightweight and packed with innovation this entry model is a must have for applications where speed, convenience and precision are the focus.

H4-7 Cordless 4V Hot Melt Glue Gun




Cordless 12V

Semi-pro/pro glue gun

Utilising the Tacwise 12V fast charge battery platform, this model carries all the features of the 4V tool but with extra power to deliver more glue with each charge.

H12-7 Cordless 12V Hot Melt Glue Gun







12 Volt Li-ion Battery

This fast charging, interchangeable battery can be used in any of our 12V range.

Code: 1582 - Battery only





High output, performance glue gun

This cordless Lithium-Ion powered glue gun gives you independence and working flexibility and is ideal for frequent tasks that call for accuracy and efficiency. Super-fast 60 second heat up time dispenses glue at a high output of 360g/h. Ergonomically designed, easy to use with a battery-powered base providing a sturdy platform to keep the gun upright eliminating any glue leaks.

H12-12 Cordless 12V Hot Melt Glue Gun





Speed and durability

For the hobby and professional alike, Tacwise hot melt glue guns and adhesives deliver quality results and bond a wide variety of materials quickly and efficiently.

Corded 150 & 202 Glue Guns

For hot and cool melt gluing

Our corded glue guns offer fast, reliable heating, tough polymer housing with ergonomic grips for comfort and an integrated stand for resting the glue gun in between applications.

150 Cool Melt Glue Gun

Code: 0465 Semi-Professional Includes: 2pcs 7.4mm x 100mm clear glue sticks

Diameter/Length 7.4mm x 100mm 0.3kg Retail Trade = 12 Units Transit = 36 Units

Safe, compact gun, ideal for hobby use, arts and crafts or general low volume applications. Cool melt offers a safer alternative with the adhesive running at a much lower temperature.



Rubber nose protector

Illuminated on/off switch (model 202)



Pressure touch feed system



150 & 202 Tool Features

The 150 and 202 models have handy features including insulated rubber nose protectors, on/off switches (illuminated for 202) and pressure touch feed systems for speed and reliability.



202 Hot Melt Glue Gun



A well balanced glue gun for maximum control and an easier output flow of glue.







Features						Auto turn off	Ergonomic grip	Fast heating system	Flat base functions as a stand	Illuminated on/off switch	Integrated wire stand	LED work light	Long power cord	Multi-finger trigger	On/off switch	Pressure touch feed system	Rechargeable lithium-ion battery	Removable 12V lithium-ion battery	Status indicator light Tough polymer lightweight body
Cordless	Code	Description																	
H4-7 Cordless 4V Hot Melt Glue Gun	1559	Compact with integr	ated 4V re	echargeabl	e battery	٠	٠	•	• •			٠		•	•	•	•	•	• •
H12-7 Cordless 12V Hot Melt Glue Gun	1560/1604	Interchangeable 12	/ battery.	LED work I	ight	•	٠	•	• •			•		•	•	•	•	•	• •
H12-12 Cordless 12V Hot Melt Glue Gun	1561	Versatile and super-	fast heat	up time		•	•	•	• •			•		•	•	•	•	•	• •
Corded	_																		
150 Cool Melt Glue Gun	0465	Compact. Works at	a safer lov	wer temper	ature		٠	•	•		٠		٠		٠	•			•
202 Hot Melt Glue Gun	0466	Semi-professional, v	vell balan	ced for ma	ximum control		•	•	•	•	•		•		•	•			•
Applications						Beading/mouldings	Book binding	Carton sealing	Decorative/general DIY	Displav/shop fitting	Exhibition/shows	Fixing gripper/thresholds	Floristry	Hobby crafts	Picture/mirror frames	Schools/education	Theatre/film scenery	Toy repairs	Upnoistery/re-upnoistery Window dressing
Cordless	Code	Description																	
H4-7 Cordless 4V Hot Melt Glue Gun	1559	Compact with integr	ated 4V re	echargeabl	e battery		٠		• •				•	•	•	•		•	• •
H12-7 Cordless 12V Hot Melt Glue Gun	1560/1604	Interchangeable 12	/ battery.	LED work I	ight		٠	•	•	•	٠		•	•	•		•		• •
H12-12 Cordless 12V Hot Melt Glue Gun	1561	Versatile and super-	fast heat	up time		•		•	•	•	٠		•	•	•		•		• •
Corded																			
150 Cool Melt Glue Gun	0465	Compact. Works at	a safer lov	wer temper	ature				•				•	•		•			
202 Hot Melt Glue Gun	0466	Semi-professional, v	vell balan	ced for ma	ximum control	•			•	•		•	•	•	•	•	•		• •
Specifications		Dimensions in mm (H x W x D)	Weight (kg)	Glue Diar	neter/Length (mi	n)	Volta	ige	Capa (Ah			ge 1 (Hrs)		Сс				ber cl s use	harge e)
Cordless	Code																		
H4-7 Cordless 4V Hot Melt Glue Gun	1559	157 x 165 x 42	0.43	7	x 150mm		4V	/	1.3	;		1.5	Up to 6 glue sticks				ks		
H12-7 Cordless 12V Hot Melt Glue Gun	1560/1604	200 x 160 x 52	0.24	7	x 150mm		12	12V 1.3			3-5				Up to 16 glue sticks				cks
H12-12 Cordless 12V Hot Melt Glue Gun	1561	205 x 176 x 52	0.28	11.75 x	150mm/300mn	n	12	12V 1.3			3-5				8 (150mm) /4 (300mr)mm)
Corded																			
150 Cool Melt Glue Gun	0465	117 x 127 x 24	0.3	7.4 x 100mm			-				-						-		
202 Hot Melt Glue Gun	0466	157 x 187 x 32	0.5	11.75 x 300mm			-		-			-					-		
Glue Sticks Specifications		Diameter & Length (mm)		ack antity	Pack Style							ι	For Jse li						
Hot Melt Glue	Code																		
Clear Hot Melt Glue Sticks	1562	7 x 150mm 100 Sticks Plain Box				H4-7, H12-7													
Clear Hot Melt Glue Sticks	0470	11.75 x 300mm	16 \$	Sticks	Retail Box						H12	2-12	2, 20	2 &	207				
Clear Hot Melt Glue Sticks	0471	11.75 x 300mm	5kg/16	60 Sticks	Carton						H12	2-12	2, 20	2 &	207				
Tan Hot Melt Glue Sticks	0472	11.75 x 300mm	5kg/16	60 Sticks	Carton		H12-12, 202 & 207												
Cool Melt Glue																			
Clear Cool Melt Glue Sticks	0476	7.4 x 100mm	12 \$	Sticks	Retail Card								150	I					

Air Nailing & Stapling

34 quality, high performance tools

We believe that design and manufacturing innovation is the key to success and we continue to refine our designs to bring you the very best tools within their class. Our aim is to develop new standards of performance utilising the most advanced aluminium, magnesium and titanium materials, to define products that do more than simply function – but that perform better and last longer.





Built for the professional

Tacwise is committed to creating the ultimate fastening product range from hand, corded, cordless and air powered equipment, combined together to provide the widest quality tools and consumables programme in Europe.


Loaded with features

Each with their own powerful features, Tacwise air tools are carefully designed for user safety, convenience and durability.









Reload indicators and rubber noses to avoid damaging softer timbers. Easy reference serial numbering makes re-ordering consumables and replacement parts easy.

Handy and easy to use controls for depth adjustment make precision tasks simple.







This small lever allows the user to quickly switch between single shot and contact trip (bump fire).

Quick release magazines of different styles mean ultra fast re-loading.

Air Nailing & Stapling 5

General Purpose & Upholstery Staple Guns



Extra Long Nose 71 Staple Tacker (71/4-16mm)



Magnesium bodied stapler taking 71 upholstery staples, with an extended 50mm nose for reaching into awkward areas. Lightweight and compact with rear exhaust, this tool is a firm favourite in the re-upholstery trade.

Extra Long Nose 80 Staple Tacker (80/4-16mm)

 Production Line
 Code: A8016LN
 BEST VALUE

 Image: Book Staples 4-16mm
 60-100
 Ikg
 Image: Carry Carry Carry Trade = 1 Unit Transit - 6 Units

Magnesium bodied stapler with an extended 50mm nose to allow for stapling into awkward areas. Lightweight and compact with rear exhaust, this tool is a firm favourite in the re-upholstery trade.



Fast and lightweight

Unrivalled quality and performance from our top selling upholstery and general purpose air staplers. From the fastest to the lightest, we have a programme that covers all applications. Tacwise has continued to refine its programme of upholstery and general stapling tools after many years of industry experience.



71 Upholstery Staple Tacker 71/4-16mm

Production Line	Code: A7116	BEST VALUE			
FIOUUCUOII LINE	Code: 1190	Includes: 120,000pcs 71 staples	NEW		
71 Staples 4-16mm 60	100 0.9kg Ca	ry Trade = 1 Unit se Transit = 10 Units			

Fast, reliable and the first choice for many professional upholsterers. Incorporating every essential feature our users have asked for. Quiet, reliable and extremely quick to load.

Premium 7	1 Sta	ple Ta	cker	71/4-16mm
Production Li	ne	Code: A71	16P	
71 Staples 4-16mm	60-100	0.8kgs	Retail	Trade = 1 Unit

This model is fast and well balanced. Designed for the production line environment. Incorporating every essential feature our users have asked for. Quiet, reliable and extremely quick to reload.





80 Upholstery Staple Tacker 80/4-16mm

Production Line	Code: A8016	V BEST VALUE
80 Staples 4-16mm 6		arry Trade = 1 Unit ase Transit = 10 Units

Fast, reliable and the ultimate first choice for many professional upholsterers. Ideal for production line use. The wide 80 series staple provides additional fastening strength for materials such as plastic sheeting. Especially popular with our European users.

Air Stapling Stapling up to 40mm

140 Staple Tacker (140/4-14mm) Professional Code: A14014V BEST VALUE (J 1 ſ 140 Staples 4-14mm 60-100 0.9kg Carry Case Trade = 1 Unit Transit = 10 Units This professional tool handles the 140 (T-50 Type) staple, commonly used in hand and electric tackers. Ideal for hand tool users tackling volume stapling tasks with standard and stainless steel staples. 140 staples listed on page 50. watch the Al4014V video

71	sta	p	e

η ι σταρι	63		
Code	Staple Length/Type	Box Qty	For Use In
0365	71/4mm	20,000	71EL, 71ELS, A7116LN, A7116V, A7116P
0366	71/5mm	20,000	71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P
0367	71/6mm	20,000	
1014	71/6mm s/steel	20,000	
0368	71/8mm	20,000	
1065	71/8mm black	20,000	
0369	71/10mm	20,000	
0373	71/10mm black	20,000	71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P
0375	71/10mm s/steel	20,000	
0370	71/12mm	20,000	
0290	71/12mm black	20,000	
0371	71/14mm	10,000	
0374	71/14mm black	10,000	
0372	71/16mm	10,000	71EL, 71ELS, A7116LN, A7116AUTO, A7116V, A7116P





80 staples 0380 80/4mm 10,000 0381 80/6mm 10,000 0382 80/8mm 10,000 0383 80/10mm 10,000 0384 80/12mm 10,000 0385 80/14mm 10,000 1141 80/16mm 10,000

80ELS, A8016V, A8016LN



Narrow Crown Staplers

3 of the best production line models

Our narrow crown programme offers outstanding performance and versatility. The C9725V is compact and fast. The D9040V is versatile, reliable and its many stand-out features puts it at the top of the class in cabinet making and garden furniture applications.

25mm Narrow Crown Stapler (97/10-25mm)

Production Line	Code: C9725\	/ BEST VALUE
97 Staples 10-25mm 60-		Carry Trade = 1 Unit

Built to last, this high performance stapler copes easily with high volume stapling. Narrow quick release nose gate and safety. Top multi-directional exhaust.






32mm Narrow Crown Stapler 90/12-32mm

Production Line	Co	de: C9032	V	BEST VALUE
90 Staples 12-32mm	() 60-100	1.2kg	Carry	


Magnesium bodied stapler offering tremendous versatility and speed of use. Top selling model with excellent performance. Narrow quick release nose gate with protector and safety. Top multi-directional exhaust.





97 narrow crown staples

Code	Staple Length/Type	Box Qty	For Use In
0302	97/10mm	5000	
0303	97/15mm	5000	C9725V. C9725VHH
0304	97/20mm	5000	69725V, 69725VHH
0305	97/25mm	5000	



90 narrow crown staples


0306	90/15mm	5000	
0312	(90/18mm divergent point)	5000	
0307	90/20mm	5000	
0313	(90/22mm divergent point)	5000	C9032V, D9040V, C9030VHH, C9040LHH, DNS50PHH, 1326
0308	90/25mm	5000	
0309	90/30mm	5000	
1144 🗕	90/32mm	5000	
0310	90/35mm	5000	
0311	90/40mm	5000	D9040V, C9040LHH, DNS50PHH, 1326


F1440L, G1450V, F1450M, 1717, F1440LHH, G1450MHH

G1450V, F1450M, 1717, G1450MHH

15,000


10,000





(actual size)





0176 **14/45mm** 0177 **14/50mm**

14/25mm

14/32mm

14/35mm

14/38mm

14 heavy duty staples galv. coated 0179 14/19mm

17 wide crown staples

0780	17/19mm	10,000	
0386	17/25mm	10,000	G1738XHH, G1738V
0387	17/32mm	10,000	

32 carton closing staples

0186	32/15mm (copper coloured)	2000	Standard carton top and bottom sealers
0187	32/18mm (copper coloured)	2000	

Corrugated fasteners

0447	CF9 9mm	2000	
0448	CF12 12mm	1750	FCF15XCB
0449	CF15 15mm	1500	

• Whilst stocks last





Heavy Duty & Wide Crown Staplers

Quick Release Mase Gate

Fast and reliable

Outstanding power and speed from our range of heavy duty and wide crown staplers. Rugged tools which are highly reliable.

Depth Control Adjust



50mm Heavy Duty Stapler 14/19-50mm



Preferred throughout the bedding and furniture industry, this durable framing tool is a first choice. Loaded with features including firing variations, depth control and a quick release nose gate in the unlikely event of a staple jam.

Carry

Case

Trade = 1 Unit

Transit = 4 Units

Air Stapler/Corrugated Fastener/Inclined Nailer



Premium 15mm Corrugated Fastener CORR. FASTENERS/9-15mm

Production Line Code: FCF15XCB



I Trade = 1 Unit Transit = 4 Units taple.

Powerful fastening tool, capable of countersinking 15mm fasteners. Easy bottom loading of any size with minor adjustment. Ideal for butt joints in cabinet/furniture frames and for door and window sash manufacturers.



Nailers & Pinners


Wide assortment of quality tools

Covering fine pins of just 12mm length up to 64mm finish nails. Meeting all your requirements.

64mm Inclined Air Nailer 15G/32-64mm



Production Line Code: GDA64V2 BEST VALUE



2kg Carry Trade = 1 Unit Case Transit = 4 Units







A

Air Pin, Brad & Finish Nailers Nailing up to 64mm / Stapling up to 40mm



23G 22mm	Неа	dless P	inne	23G PINS/12	2-22mm
Production Li	ne	Code: A64	22V	BEST VALUE	
23G 'A64' 12-22mm	60-100	0.8kg	Carry Case	Trade = 1 Unit Transit = 10 Units	

Built for industrial use, featuring an auto adjusting magazine with a 100 pin capacity. This model also boasts a moveable exhaust top cap, safety trigger lock mechanism and because it operates between 60-100 PSI, only a small compressor is needed.

23G 35mm	Head	less P	inner	23G PINS/12	-35mm	N
Production Li	ne	Code: 17	46	BEST VALUE		
) 23G 'A64' 12-35mm	(J) 60-100	1.0kg	Retail	Trade = 1 Unit		

This quality, lightweight tool is perfect for fixing fine beading. Ultra slim nose for accurate pin placement. No adjustment is required to fire pins of different lengths. Rear exhaust, double trigger safety system and high durability driver.





32mm Brad Nailer (180/10-32mm) (18G/10-32mm)				
Production Line	Code	C1832V	BE	ST VALUE
∬ 180 (18G) Nails 10-32mm	() 60-100	1.1kg	Carry Case	Trade = 1 Unit Transit = 6 Units

This hugely popular lightweight tool is accurate and reliable and offers tremendous value. Compact and versatile it can be bump fired with its contact trip valve. Fires up to 5 shots per second.

50mm Brad Nailer (180/20-50mm) (18G/20-50mm)





All professional fully featured tool including a depth adjuster. Comfortable fast and lightweight. Specified by trade professionals throughout Europe, this model is already a Tacwise best seller.







50mm Hardened Finish Nailer

15G/15-50mm (160/15-50mm) (16G/15-50mm)

Production Line	Code:	EHS50V	BE	est value
15G Hard Steel	() 70-120	2.4kg	Carry	Trade = 1 Unit

Firing both hardened 15G and any 16G (160) straight finish nails from 15-50mm, this specialist nailer is one of a kind. Featuring a convenient depth adjustment wheel and quick release nose gate, it will drive fasteners into wood and concrete surfaces with speed. With a rubber handle grip and handy adjustable exhaust cap, this finish nailer is comfortable and easy to use.





Offering excellent value and widely used in the furniture manufacturing industry, this ergonomic model delivers peak performance. Fast and accurate, this finish nailer comes with a flush nose designed to avoid obstructing tool access in tight spaces. With essential user features it's reliable and demanded for volume nailing tasks.



50mm Combi Nailer/Stapler

180/20-50mm 18G/20-50mm 90/15-40mm				
Production Line	Code:	1326	BEST VA	LUE
180 (18G) Nails 20-50mm 90 Staples 15-40mm	() 70-120	1.7kg	Carry Case	Trade = 1 Unit Transit = 6 Units

A fast and versatile air nailer/stapler firing both 18G nails and 90 type narrow crown staples. Comes with a quick release nose gate, depth adjuster and 360° adjustable exhaust port as standard. This high-quality air-powered nailer/stapler is ideal for a huge range of tasks.



180 (18G) nails



(,		
Code	Nail Length/Type	Box Qty	For Use In
0205	180(18G) selection pack	4000	C1832V, DGN50V, DGN50LHH, DGN50VHH
0359	180(18G)/15mm	2000	C1832V
0360	180(18G)/20mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH, 1326
0361	180(18G)/25mm	1000	
1066	180(18G)/25mm s/steel	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH, Ranger 2 18G, 1326
0362	180(18G)/30mm	1000	C1032 V, DUNSOV, DUNSOLAA, DUNSOVAA, NAIIYEI 2 100, 1320
1067	180(18G)/30mm s/steel	1000	
0363	180(18G)/32mm	1000	C1832V, DGN50V, DGN50LHH, DGN50VHH, 1326
0364	180(18G)/35mm	1000	
1068	180(18G)/35mm s/steel	1000	DGN50V, DGN50LHH, DGN50VHH, Ranger 2 18G, 1326
0747	180(18G)/40mm	1000	- Dansov, Dansolinn, Dansovnn, Raligel 2 186, 1328
1156 🗕	180(18G)/50mm	1000	

18G brad nails

		0392	(18G/10mm)	5000	
		0393 18G/13mm	(18G/13mm)	5000	- C1832V
	NEW	1724	(18G/14mm)	5000	010327
		0394	(18G/15mm)	5000	
		0395	(18G/20mm)	5000	C1832V, DGN50V
		0396	(18G/25mm)	5000	
		0397	(18G/30mm)	5000	C1832V, DGN50V, Ranger 2 18G
52		0398	(18G/32mm)	5000	
=		0399	(18G/35mm)	5000	
		0400	(18G/40mm)	5000	DGN50V, Ranger 2 18G
	_	0401	(18G/50mm)	5000	
Ц	NEW	1708	(18G/15mm)	4000	C1832V
	NEW	1709	(18G/20mm)	4000	
V	NEW	1710	(18G/25mm)	4000	C1832V, DGN50V, 1326
	NEW	1711	(18G/30mm)	4000	- C1032V, DUNSUV, 1320
	NEW	1712	(18G/32mm)	4000	
	NEW	1713	(18G/35mm)	4000	
	NEW	1714	(18G/40mm)	4000	DGN50V, 1326
	NEW	1715	(18G/50mm)	4000	

(actual size)

(actual size)

▲ 10mm

♦ 50mm

Nail = Head



18G angled brad nails (500 Series)


0823	500/20mm	5000	
0824	500/25mm	5000	
0826	500/35mm	5000	
0827	500/40mm	5000	BeA SKAM 350-226C
0829 🗕	500/50mm	5000	
1131	500/20mm s/steel	1000	
1135	500/50mm s/steel	1000	

• Whilst stocks last



160 (16G) stainless steel finish nails

Code	Nail Length/Type	Box Qty	For Use In	
1096	(160/(16G)32mm s/steel	1000		
1097	(160/(16G)32mm s/steel	1000	DFN50V, FFN64LHH, GFN64V, FCT50LHH, Ranger 2 16G	
1098	160/(16G)32mm s/steel	1000		
16G finis	sh nails			
0665	16G/20mm	2500		
0666	16G/25mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH, ESH50V	
0293	16G/30mm	2500		
0294	16G/32mm	2500		
0295	16G/35mm	2500		
0296	16G/38mm	2500	DFN50V, FFN64LHH, GFN64V, FCT50LHH, Ranger 2 16G, ESH50V	
0319	16G/40mm	2500	Di N30V, TI N04LIIII, di N04V, 1 0130LIIII, hangel 2 100, E3130V	
0297	16G/45mm	2500		
0298	16G/50mm	2500		
0299	16G/55mm	2500		
0300	16G/60mm	2500	FFN64LHH, GFN64V, Ranger 2 16G	
0301	16G/64mm	2500		






NEW 15G hardened finish nails

1530	15G/30mm	1500	
1531	15G/35mm	1500	
1532	15G/40mm	1500	EHS50V
1533 🗕	15G/45mm	1500	
1534	15G/50mm	1500	

16G angled finish nails



0769	16G/32mm	2500	
1222	16G/32mm s/steel	2500	
0770	16G/38mm	2500	
1223	16G/38mm s/steel	2500	
0771	16G/45mm	2500	DeWalt [®] DC618 & DCN660, Paslode [®] IM250A & IM65A F16 Nailers.
1224	16G/45mm s/steel	2500	Ranger 2 16G Inclined
0772	16G/50mm	2500	
1225	16G/50mm s/steel	2500	
0773	16G/63mm	2500	
1226	16G/63mm s/steel	2500	



15G 'D' h	G 'D' head inclined finish nails						
0402	DA13/25mm	4000	FBA50VCB				
0403	DA15/32mm	4000					
0404	DA17/38mm	4000	FBA50VCB, GDA64V, GBA64LHH, GDA64V2				
0405	DA19/44mm	4000	- FDA30VCD, dDA04V, dDA04LNN, dDA04V2				
0406	DA21/50mm	4000					
0407	DA25/64mm	4000	GDA64V, GBA64LHH, GDA64V2				

Whilst stocks last

7 High performance coil nailers

Unrivalled

Most Tacwise coil nailers fire 4+ nails per second and can be used single-handedly. This is because lightweight magnesium is used to manufacture many of the tool bodies and triple hardened internal parts facilitate rapid firing and excellent durability. Ergonomic design provides great balance and comfort. Neat touches, such as external top cap crash bars help to ensure less downtime than other nailers.

Versatility

Popular for traditional nailing applications such as building sheds, fence panels and pallets. Coil nailers are a brilliant time-saving solution for any number of nailing applications where speed and efficiency are desirable. High capacity magazines contain a large volume of nails and offer continuous effective operation.

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity and makes coil nailing the preferred option compared to strip nailers, which only load around 100 nails at a time.

All Tacwise coil nailers up to 90mm are light enough for single-handed operation.











Coil Nailers

Serious About Coil Nailing

Tacwise places a great deal of focus on this important product category, with an extensive range covering most major and niche applications. We also have a comprehensive fastening programme to meet the demands of our dealer network and their largest users.


50mm Mini Coil Nailer

An exceptional tool for 2.1 diameter round head nails. Weighing 1.5kg it will still countersink a 45mm ring shank nail. Compact design with a single or bump fire trigger. Very popular in the fencing, shed and flooring industry. Will also load plastic collated coil nails 27-50mm. Tool now supplied in silver colour and not orange.





55mm Coil Nailer



The FCN55V Coil Nailer allows you to change between both conical and flat top coils, without the need for adjustment. Supplied with a newly improved lightweight magazine, offering extra strength and reliability. Lightweight at just 2.4kg, this tool can fire up to 57mm nails with ease.

57mm Coil Nailer



An extremely heavy duty workhorse, this tough production line tool has a highly developed construction and specification, firing approximately 400 nails without reloading. Contact trip trigger. Suitable for exhibition, pallet, crate and packaging industries.







70mm Coil Nailer



This tough production line tool has a highly developed construction and specification, firing up to 300 nails without reloading. Contact trip trigger. Tool ideal for the pallet and packaging industries.

83mm Coil Nailer

Production	ı Line	Code: H	ICN83P	BEST VALUE
2.5-3.3 Flat Coil	()	3.9kg	Carry	Trade = 1 Unit
Nails 40-83mm	70-120		Case	Transit = 2 Units

Robust traditional tool for reliable and tough continuous nailing. Especially hardened working parts ensure a long and productive life. Developed for the rugged pallet and case industries in particular.



90mm Air Coil Nailer



Extremely versatile, this tool accepts a wide range of nail diameters and lengths, firing up to 275 nails in a single or bump firing mode. Super lightweight magnesium alloy body for the ultimate power to weight ratio. Constructed for a range of heavy-duty and manufacturing applications.









Put to the test

We admit it; we're tough on our products. We have to be when they're used in busy industrial environments. They need to be able to withstand the toughest treatment, which is why we painstakingly stress test every new item and why we then manually test every single tool.

Outstanding Quality and Performance

Sophisticated progressive tooling, intelligent electronic engineering and a commitment to precision and detail, create the greatest air tacker programme available worldwide. Our dedication to quality begins in the initial stages of design with every component machined to extraordinary precision for years of trouble-free use.

High Performance Coil Nails

Increasingly demanded within the construction industry, the ability to fire up to 400 nails without re-loading increases productivity.

Point Varieties	3	Shank Varieties			Nail Surface Treatments		Euro code 5 CE Service class 2 (CE2/12+)			
Diamond	Blunt	Smooth Shank - smooth plain surface	Bing Shank	Screw Shank	Bright: Untreated (no coating)	Galvanised (Galv.) Electroplated zinc coating approx. 6-8 microns	Extra Galvanised (Extra Galv.) Rust protected by electroplated zinc coating 12+ microns			

Code

1229

0994

Coil nails wire collated flat top Nail Length/Type


2.1 25mm galv., ring

2.1 30mm bright, ring

2.1 32mm galv., ring

2.1 35mm bright, ring

2.1 35mm galv., ring, blunt



	0995	2.1 40mm bright, ring	14,400	
	0996	2.1 40mm galv., ring	14,400	FCN50LHH2, GCN57P, FCN55V, FCN65V, HCN65P
	0997	2.1 45mm bright, ring	14,400	
	0998	2.1 45mm galv., ring	14,400	
	0999	2.1 50mm bright, ring	14,400	
	0495	2.1 50mm galv., ring	14,400	
	0279	2.3 50mm bright, ring	9000	GCN57P, FCN55V, HCN65P, GCN70V
	0421	2.5 45mm bright, ring	9000	FCN55V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH
	0422	2.5 50mm bright, ring	9000	
	0423	2.5 50mm galv., ring	9000	FCN55V, HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH, JCN90V
	0424	2.5 55mm bright, ring	9000	
	0425	2.5 60mm bright, ring	9000	
	0427	2.5 64mm bright, ring	9000	
	1074	2.5 64mm bright, smooth	9000	HCN65P, FCN65V, GCN70V, HCN83P, JCN90XHH, JCN90V
	0428	2.5 64mm galv., ring	9000	
>	1548	2.5 64mm s/steel, ring	9000	
	1093	2.5 70mm bright, smooth	9000	
	0429	2.7 64mm bright, ring	6000	HCN65P, GCN70V, HCN83P, JCN90XHH, JCN90V
	0430	2.7 75mm bright, ring	6000	HCN83P, JCN90XHH, JCN90V
	0777	2.8 50mm CE2/12+ micron galv., ring	4000	
	0964	2.8 64mm CE2/12+ micron galv., ring	4000	HCN65P, GCN70V, HCN83P, JCN90XHH, JCN90V
	1762	2.8 75mm galv., ring	4000	
	0965	2.8 83mm bright, ring	4000	HCN83P, JCN90XHH, JCN90V
	0433	3.1 90mm CE2/12+ micron galv., ring	4000	JCN90XHH, LCN130V, JCN90V
	1021	3.1 90mm bright, ring	4000	
	1036	3.3 65mm CE2/12+ micron galv., ring	4000	HCN83P, JCN90XHH, JCN90V
	1035	3.3 75mm CE2/12+ micron galv., ring	4000	HCN83P, JCN90XHH, LCN130V, JCN90V
	1154 🗕	3.3 98mm bright, ring	4000	LCN130V
	1155	3.8 130mm bright, screw	1500	

Box Qty

14,400

14,400

14,400 14,400 For Use In

GCN57P, FCN55V

FCN50LHH2, GCN57P, FCN55V

Coil nails wire collated conical top

	1128	2.1 22mm galv., ring, blunt	14,400	FCN50LHH2
	1000	2.1 27mm galv., ring, blunt	14,400	DCN50LHH2, FCN50LHH2, FCN55V
N	1002	2.1 32mm galv., ring	14,400	
	1545	2.1 32mm s/steel, ring	14,000	
	1003	2.1 32mm galv., ring, blunt	14,400	
	1516 🗕	2.1 35mm galv., ring	14,400	
	1004	2.1 38mm bright, ring	14,400	
N	1005	2.1 38mm galv., ring	14,400	
	1546	2.1 38mm s/steel, ring	14,400	DCN50LHH2, FCN50LHH2, FCN55V, FCN65V
	1006	2.1 38mm galv., ring, blunt	14,400	
N	1009	2.1 45mm galv., ring	14,400	
	1547	2.1 45mm s/steel, ring	14,400	
	1010 🗕	2.1 45mm galv., ring, blunt	14,400	
	1011	2.1 50mm bright, ring	14,400	
	1012	2.1 50mm galv., ring	14,400	





Whilst stocks last



Strip Nailers

Perfect for roofing and framing

The ultimate range of angled strip nailers, offering sheer power, outstanding performance and reliability. An essential for all those tough jobs.

90mm 34° Angled Strip Nailer

TACWISE



Extremely powerful, reliable and with virtually no recoil this 34° 'D' head strip nailer is very popular with timber frame house builders and is perfect for a wide variety of first fix roofing applications.



A IN.



79

90mm 21° Angled Strip Nailer



Heavy-duty 21° inclined strip nailer, with a single or bump firing mode. Designed to bring power and reliability to a wide variety of structural first fix joinery and framing applications. The lightweight angled magazine provides easy access in all frame construction applications day in, day out.




Strip Nails



Strip nails plastic collated (22° inclined round head)

	- p		
Code	Nail Length/Type	Box Qty	For Use In
0435	2.9 50mm CE2/12+ micron galv., screw	3000	
0436	3.1 90mm CE2/12+ micron galv., screw	3000	JSN90MHH2. JSN00LHH. KSN90V
0437	3.3 65mm CE2/12+ micron galv., screw	3000	
0438	3.3 75mm CE2/12+ micron galv., screw	3000	
0439	3.4 100mm CE2/12+ micron galv., screw	3000	JSNOOLHH



Strip nails paper collated (34° inclined 'D' head)

	1124	2.8 50mm CE2/12+ micron galv., ring	3000	
	1125	2.8 65mm CE2/12+ micron galv., ring	3000	
	1120	3.1 65mm CE2/12+ micron galv., ring	2200	
	1121	3.1 75mm CE2/12+ micron galv., ring	2200	
	1122	3.1 90mm CE2/12+ micron galv., plain	2200	
	1123	3.1 90mm CE2/12+ micron galv., ring	2200	KDH90V, KDH90XHH, JDH90FHH
N	1752	2.8 50mm CE2/12+ micron galv., ring	1600	
N	1754	2.8 50mm bright, ring	1600	
N	1753	2.8 65mm CE2/12+ micron galv., ring	1600	
N	1721	3.1 65mm CE2/12+ micron galv., ring	1600	
N	1722	3.1 75mm CE2/12+ micron galv., ring	1600	
N	1723	3.1 90mm CE2/12+ micron galv., ring	1600	



Positive p	lacement nails paper collated (34	° inclined	round head)
0004	0.75.00 mans OF/10, maintain make wind	0000	ГРИООТИИ

RH381F



Variations of air tool triggers

Any tool likely to be used to fire higher volumes of fasteners at speed will almost always be capable of bump firing or (in the case of very small upholstery type tools) require no additional safety system other than the standard single or double trigger. A sequential or single shot trigger will usually be fitted where exact placement of the fastener is most important.



Sequential firing

This system also requires the nose safety to be depressed against the surface. However, this MUST be done prior to activating the trigger or the tool will not fire. This means that even if the trigger is held up, the tool will not fire if the safety contacts a surface either accidentally or on purpose.

With a sequential safety it is possible for the tool to continue to be fired all the time the nose safety is depressed against the work surface. Once released the exact same sequence (hence sequential firing) must be repeated in order to fire any additional fastenings.

For speed firing, you may choose to leave the nose pressed against the work surface with the nose safety depressed and slide the tool along the work piece whilst activating the trigger.



Safety trigger This is purely a safety locking device whereby the main trigger cannot be activated until the secondary trigger is depressed.

Single shot firing

This safety mechanism will only ever allow one fastener to be fired at a time. To fire the next fastener, the nose safety needs to be lifted from the work surface and the trigger allowed to reset.

Contact trip (bump firing)

This allows a fastener to be fired whenever both the nose safety trip and trigger are activated simultaneously. Consequently, fasteners can be fired at speed by holding up the trigger and repeatedly bumping the nose against the workpiece (referred to as bump firing). Effectively the tool drives a fastener each time it is 'bumped'.

The contact trip (nose safety) still prevents a fastener from being fired if it is not depressed against the work surface, however, if the trigger is activated and the nose safety trip accidentally touches against an object or person, a fastener will be fired. Therefore, UNDER NO CIRCUMSTANCES should an operator hold or carry a tool around with the trigger depressed.

Unless reasonable downward pressure is maintained on the nose safety after firing, it is possible for certain tools to recoil back from the work surface and then fire again on re-contact (only if the operator continues to hold up the trigger).

To prevent this from happening, these tools should be allowed to recoil far enough to release the contact trip and avoid a repeat cycle of the driver, which fires a fastener. It is possible to purchase a single shot trigger (usually red) for most contact trip tools in the Tacwise range – please contact our service department for details.

Choosing the correct fastening length

The type and thickness of the material you are using will determine the length of staple or nail that is needed.

General Rule


When stapling and nailing, the fastener should be 3 times longer than the material to be fixed. If you are nailing, a further 5mm should be added to the length of the nail.

Hardwood/Material


When stapling and nailing into hardwood, a staple that is twice the depth of the material you are fixing will be adequate. If you are nailing make sure that the nail is 3 times the length of the material.

Thin Material/Fabric

When stapling into thin material or fabric, a staple that is 4mm longer than the material is perfect. When nailing, choose a nail that is 6mm longer than the material.







	Stapl Gene	ing M ral Pu	achine rpose	es & Uph	nolster	у	Narro Crow			Heavy Duty, Wide Crown & Corr. Fastener						
Specifications	A7116LN	A7116V	A7116P	A8016V	A8016LN	A14014V	C9725V	C9032V	D9040V	G1450V	F1450M	F1450V	G1738V	FCF15XCB		
Depth (mm)	230	218	218	218	230	235	248	273	302	368	360	376	330	300		
Width (mm)	45	43	43	43	45	46	55	67	88	97	78	108	80	87		
Height (mm)	220	150	152	150	220	159	192	231	253	290	272	282	252	270		
Weight (kg)	1.1	0.9	0.8	0.9	1.1	0.9	1.2	1.2	1.7	2.0	1.9	2.5	2.4	2.6		
Takes staple/nail type	71	71	71	80	80	140	97	90	90	14	14	14	17	CF		
Fasteners length (mm)	4- 16	4- 16	4- 16	4- 16	4- 16	4- 14	10- 25	12- 32	15- 40	19- 50	19- 50	19- 50	16- 38	9- 15		
Capacity	180	180	180	150	150	150	125	100	100	150	150	160	140	80		
Max dBA sound/noise	77	77	77	77	77	77	86	88	88	90	85	96.5	86	80		
PSI	60- 100	60- 100	60- 100	60- 100	60- 100	60- 100	60- 100	60- 100	70- 120	70- 120	70- 120	70- 120	70- 100	75- 110		
Trigger	SS	SS	SS	SS	SS	SS	CT	CT	(CT/ S	(CT/ S	CT	(CT/ S	CT	СТ		
Features																
360° adjustable exhaust port								٠	•	•	•	•	•	•		
Bottom loading	•	٠	٠	٠	•	•								•		
Depth control countersinking								٠	•	•		•	•			
Double safety trigger		٠		٠												
Easy top loading system										•	•	•	•			
Extra long nose	•				•											
High capacity magazine/nail drum	•	•	•	٠	•	•	•	•	•	•	•	•	•			
High durability driver blade system	•	•	•	٠	•	•	•	•	•	•	•	•	•	•		
Neat rear exhaust system	•	٠	•	٠	٠											
Non-marking nose								•	•							
Open (viewable) magazine system										•	٠	•	•			
Quick release nose gate							•	٠	•	•		•	•			
Quick release reloading system	•	•	•	•	•	•	•	•	•					•		
Safety contact							•	•	•	•	•	•	•	•		
Side loading							•	•	•							
Single shot trigger	•	٠	•	•	•	•	•									
Slender length nose	•	٠	٠	•	•	•	•									
Soft rubber safety grip	•	٠	•	٠	•	•	•	•	•	•	•	•	•	•		
Staple/nail refill window	•	•	•	٠	•	•		•								

(ST) Safety Trigger (CT) Contact Trip (Bump Fire) (SE) Sequential (SS) Single Shot (ST) Single Shot/Contact Trip (St) Contact Trip/Sequential (SS) Single Shot/Auto

BEST VALUE



	Naile & Pin									Coil Naile	rs						Strip Naile	rs
Specifications	A6422V	1746	C1832V	DGN50V	EHS50V	DFN50V	1326	GDA64V2	GFN64V	DCN50LHH2	FCN55V	GCN57P	HCN65P	GCN70V	HCN83P	JCN90V	V06HDX	V06NSX
Depth (mm)	205	240	273	273	321	302	266	340	292	260	305	380	305	330	305	360	470	530
Width (mm	45	66	67	67	91	88	67	100	88	108	130	130	130	132	132	127	150	124
Height (mm)	170	187	228	249	290	270	262	315	295	284	302	290	312	308	340	362	364	364
Weight (kg)	0.8	0.9	1.1	1.2	2.4	1.7	1.7	2	1.8	1.5	2.4	2.7	2.5	3.7	3.9	3.5	3.8	3.7
Takes staple/nail type	23G/ 0.64	23G/ 0.64	18G/ 180	18G/ 180	15G	16G/ 160	18G/ 90	15G	16G/ 160	2.1	2.1- 2.5	2.1- 2.3	2.3- 2.9	2.3- 2.9	2.5- 3.3	2.5- 3.3	2.8- 3.7	2.87- 3.33
Fasteners length (mm)	12- 22	12- 35	10- 32	20- 50	15- 50	20- 50	15- 50	32- 64	20- 64	22- 50	25- 57	25- 57	32- 65	40- 70	38- 83	50- 90	50- 90	50- 90
Capacity	100	100	100	100	100	100	100	100	100	400	300- 400	300- 400	250- 350	250- 350	250- 300	225- 275	75- 95	65- 70
Max dBA sound/noise	77	77	81	86	82	86	91	99.5	89	83	96	96	96	83	95	108	86	106
PSI	60- 100	60- 100	60- 100	60- 100	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120	70- 120
Trigger	SE	ST	(CT)	(CT)	(CT)	CT	CT	(CT/ S	(CT/ S	(SS/ CT	(CT/ S	(CT)	(CT/ S	(CT)	(CT)	(CT/ S	(CT/ S	(CT/ S
Features																		
360° adjustable exhaust port	٠		٠	•	٠	٠	٠	٠	٠	٠	•	•	•		•	•	•	•
Bottom loading																		
Depth control countersinking			•	٠	٠		٠	٠	٠	٠	•		•			٠	•	•
Double safety trigger		٠																
Easy top loading system							٠											
Extra long nose																		
High capacity magazine/nail drum	•	•	٠	•	٠	•	•	•	•	•	•	•	•	•	•	•	•	•
High durability driver blade system	•	٠	•	٠	٠	٠	٠	٠	٠	٠	٠	٠	•	٠	٠	٠	•	•
Neat rear exhaust system		٠																
Non-marking nose		٠	•	•			•	٠	٠		٠		•			•	٠	•
Open (viewable) magazine system								٠	٠	٠	٠		•			٠	•	•
Quick release nose gate			•	٠	٠		٠	٠	٠									
Quick release reloading system	•	•	•	٠	٠	•	٠											
Safety contact			٠	•	٠	•	٠	٠	٠	٠	•	•	•	•	•	•	•	•
Side loading	•	•	٠	•	•	•												
Single shot trigger								٠	٠	•	٠		•			•	•	•
Slender length nose	٠	•		٠		٠			٠	•								
Soft rubber safety grip	٠	٠	٠	٠	٠	٠	٠	٠	٠	٠	٠	٠	•	٠	•	٠	•	•
Staple/nail refill window		•		٠	٠		٠											

At a Glance Air Tools

	Stap Gene	ling N eral Pu	lachir urpose	ies e & Up	oholst	ery	Narro Crow			Heavy Duty, Wide Crown & Corr. Fastener					
Applications	A7116LN	A7116V	A7116P	A8016V	A8016LN	A14014V	C9725V	C9032V	D9040V	G1450V	F1450M	F1450V	G1738V	FCF15XCB	
Attaching mesh netting to wood	•	٠	٠	٠	٠	٠	•	٠	٠						
Bed frames										٠	•	٠			
Cabins, mobile homes, caravans							•	٠	•	٠	•	٠	•	٠	
Cane/rattan furniture							٠	٠	•						
Carpet/underlay/gripper						٠									
Coffin linings	•	٠	٠	٠	٠	٠									
Coffin manufacture						٠	٠	٠	•	•	•	٠	٠	٠	
Drawer/cabinet bottoms							•	٠	•						
Exhibition/show construction						٠	٠	•	•						
Exhibition/show upholstery	•	٠	•	٠	•	٠									
Fencing										٠	•	٠			
Fixing underlayment						٠		٠	•						
Furniture frames										٠	•	٠			
Insulation and lining	•	٠	٠	٠	٠	٠									
Kitchen and bedroom furniture							•	٠	•	•	•	٠			
Office screens	•	٠	٠	٠	٠	٠									
Pallet/packing case manufacture										٠	•	٠	•		
Panelling							•	•	•						
Pelmets, blinds and awnings	•	٠	•	•	•	٠									
Pet cages, runs and enclosures						٠	•	•	•						
Plasterboard								•	•						
Presentation boxes							•	٠	•						
Roofing felt				•	•	•									
Sheds and garden buildings						•				•	•	•			
Shoe repair							•	•	•						
Sign manufacture				٠	•				•	•	•	•	•		
Staircases and banisters								•	•	•	•	•			
Subflooring and plywood								•	•						
Theatre and film scenery	•	•	•	•	•	•	•	•	•	•	•	•		•	
Trellis work									•						
Tubs and barrels										•	•	•	•		
Upholstery and re-upholstery	•	•	•	•	•	•									
Window display/shop fitting	•	•	•	•	•	•	•	•		•	•	•	•		
Window frames and beading														•	

BEST VALUE



	Naile & Pir	ers nners								Coil Naile	ers						Strip Naile	ers
	A6422V	1746	C1832V	DGN50V	EHS50V	DFN50V	1326	GDA64V2	GFN64V	DCN50LHH2	FCN55V	GCN57P	HCN65P	GCN70V	HCN83P	JCN90V	KDH90V	KSN90V
Beading and picture/mirror frames		•	•	•	_		•		•	_		-	_	-				
Boat building				•				•	•								•	
Cabins, mobile homes, caravans	•	•		•				•	•	•	•	•	•	•	•		•	
Cable drums and steel skids																		
Cane/rattan furniture				•														
Coffin manufacture		•	•	•			•	•	•									
Construction					•								•	•	•	•	•	•
Decking								•	•	•	•	•		•	•		•	
Display and shop fitting	•	•	•	•	•	•	•	•	•									
Door frames and skirting			•	•	•	•	•	•	•									
Exhibition/show construction			•	•	•	•	•	•	•	•				•				
Fencing			•	•		•		•	•	٠	•	٠	•	•		•	•	•
Fire surrounds	•		•	•	•													
Fixing gripper and thresholds					٠	٠												
Furniture/woodwork assembly	•		•	•			•	٠	•									
Insulation and lining									•									
Kitchen and bedroom furniture	٠	٠	٠	٠		٠	•	٠	•									
Pallet/packing case manufacture								•		•	•	•	•	•	•	•		•
Panelling			٠	٠	•	٠	•	٠	•									
Pet cages, runs and enclosures			٠	٠			•	٠	•	٠								
Pine furniture manufacture		٠	٠	٠		٠	•	٠	•									
Presentation boxes	•	٠	٠	٠					٠									
Saunas			٠	٠		٠		٠	٠									
Sheds and garden building			٠	٠		٠		٠	٠	٠	•	٠	•	٠	•	٠		•
Shoe repair			٠	•														
Skirting boards/dado to masonry					٠	•												
Soft and medium wood floors	٠			٠		٠	•	٠	•							٠		
Staircases and banisters			٠	٠		٠	٠	٠	٠									
Subflooring/boarding out				٠	٠		٠			٠			٠	٠				
Suspended ceilings						٠												
Theatre and film scenery			•	•	•		•	•	•					٠				
Timber framing													٠	٠	•	•	•	٠
Tongue and groove flooring				٠	٠			•	٠									
Toy manufacture	•	•	٠	•			•											
Trellis work										٠			٠					
Window frames and beading	•	•	•	•				•	٠									

Browse By Project Find the right tool with ease

Search on **Tacwise.com** and whether you're an enthusiastic DIYer or a professional tradesperson, our 'browse by project' categories make finding the right tool for the job quick and easy.

From carpet underlay and upholstery to woodwork assembly, roofing, framing and DIY, Tacwise has the perfect tool for every application.

















Construction & Manufacturing



Roofing, Sheeting & Insulation

Key														
PSI		\bigcap		ITT	Pack Style									
PSI value	Weight of tool	Staple type	Pin/nail type	Strip/coil type	Packaging type	Number of units								
DI	<mark>Y/Semi-</mark> P	Pro	Sem	n <mark>i Profess</mark> i	ional	F	Professional		Production Line	<mark>;</mark>				
	lity, affordab d for occasio			lity tool but lous, repetiti			tile and durable to juent stapling/nail		Offers speed and reliability for tough and repetitive work					
ST) Safet	ty Trigger	CT) Cont	act Trip (Bun	np Fire)	(SE) Sequer	ntial	Single /Shot	(SS/ CT) S	Single Shot/Contact Trip	(Cf/) Contact Trip/Sequential				

Inch/mm Conversion Chart

mm	4	5	6	8	10	12	14	16	17	18	19	20	22	25	28	30	32	35	38	40	45	50	55	60	64	65	70	75	83	90	100	130
Inches	5/ 32	3/ 16	1/4	5/ 16	3/8	1/2	9/ 16	5/8	11/ 16	23/ 32	3/4	13/ 16	7/8		1 1/8	1 3/16	1 1/4	1 3/8	1 1/2	1 9/16	1 3/4		2 3/16	2 3/8	2 1/2	2 9/16	2 3/4		3 1/4	3 3/8	4	5 1/8







REPAIR, REUSE, RECYCLE



TRUST

Tacwise Group Plc

tacwise.com

sales@tacwise.com

Copyright © Tacwise Group Plc. All rights reserved. Errors and Omissions Excepted.

Every attempt has been made to give accurate information, but it is our policy to continually improve our products therefore we reserve the right to withdraw or amend the product specification in any way. Under such circumstances wherever possible an alternative or substitute product may be offered.

