

Product Data Sheet



COLSON LEGRAND

Colson Polyamide 12 Cable Tie 262mm x 9mm Black

REF. 031916 | EAN. 3414971132191

> [Link to e-catalog product sheet](#)

Technical characteristics

Band width	9 mm
Length belt/tape/tie	262 mm
Tie thickness	2 mm
Min. tensile strength	530 N
Operating temperature	-40-85 °C
Mounting temperature	-30-85 °C
Model	External tothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide flame retardant

Surface protection	Untreated
UV-stable according to ASTM D6779	Yes
Halogen free	Yes
Colour	Black
Transparent	No
Fluorescent	No
Text strip	None
Solvable fastener	No
Type of fastening	Dowel
UL approval	Yes

Documents

Technical documentation

- F00139EN-10.pdf | PDF (1.16Mo)
- F002529EN-00.pdf | PDF (0.44Mo)

Agreements & certificates

- LGRP-00673-V01.01-EN.pdf | PDF (0.56Mo)