



CGN99H/Large

Hypercardioid condenser gooseneck microphones

The CGN99 H/S and CGN99 H/L, part of the DAC Series, are condenser gooseneck microphones with a hyper cardioid polar pattern. They are a good choice for all situations when unwanted noise arrives from the sides or where people talk into the microphone from greater distances. The rugged gooseneck is available in two different lengths: C/S - 30cm (12in); C/L - 50cm (20in) and ideal for fixed and mobile installations. CGN99 H/S and CGN99 H/L come with an integrated XLR phantom power adapter with 250Hz bass roll off. The phantom power adapter connects to any standard mixer input with 9V to 52V power supply.

General Specifications

Audio frequency bandwidth: 50 - 19000 Hz

Equivalent noise level: 21 dB-A

Sensitivity: 12 mV/Pa

Signal-to-Noise: 73 dB-A

Electrical impedance: 600 Ohms

Recommended load impedance: 2000 Ohms

Polar Pattern: Hyper cardioid

Powering Interface

Voltage: 9 to 52 V

Current: 3 mA

Dimensions

Height: 380 mm

Diameter: 13.5 mm

Net Weight: 160 g

Design

Finish: black

Audio Output

Type: Balanced XLR

GenderMale

Contacts3-pin

Box Content:

1 x CGN99H/L Microphone

1 x Windscreen