



Circuit breaker enclosure, PowerPacT M/P, 300A to 800A, 2 and 3 pole, NEMA 12K, steel

M800AWK

# Main

Cincuit Bussless Tons		
Circuit Breaker Type	PGL	
	PLL	
	MJL	
	MGL	
	PJL	
	PKL	
Breaker Compatibility	Circuit breaker M 3P	
	Circuit breaker P 2P	

## Complementary

Rated Current	300800 A
Poles Description	3P 2P
Enclosure Material	Steel
Height	40.83 in (1036.96 mm)
Width	20.75 in (527.05 mm)
Depth	9.50 in (241.3 mm)

#### **Environment**

Product Certifications	UL
	CSA

#### **Environmental**

|--|

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.91 in (32.8 cm)
Package 1 Width	22.40 in (56.9 cm)
Package 1 Length	44.29 in (112.5 cm)
Package 1 Weight	86.99 lb(US) (39.46 kg)



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Toxic Heavy Metal Free
<b>②</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations