## DIY Right Angle 4mm Banana Plug Solderless Screw





## Applications

General purpose electric and electronic testing, controlling and measuring.

## **Specifications**

- Connector Type Connector Mounting Termination Type Voltage Rating Current Rating Resistance
- : Right Angle 4mm Banana Plug
- : Cable Mount
- : Solderless Screw
- : CAT III 1000V
- : 20A
- : <10mΩ

## Part Number Table

Description	Insulator Colour	Part Number
DIY Right Angle 4mm Banana Plug, Solderless Screw Wire Attachment, 1000V, 20A	Blue	72-13666
	Yellow	72-13668
	Green	72-13674

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

